

KERN FK 10



Robust, digital force gauge for tensile and compressive force measurements



Functions

Hold function	✓
Peak function	✓

Power Supply

Supplied power supply	Power supply & battery included
Plug-in power supply type	Power adapter
Plug-in power supply / adapter for countries - included with the delivery	EURO UK US CH
Plug-in power supply / adapter for countries - optional	UK US
Input voltage power supply / power [Max]	100 V - 240 V
Input voltage device / power [Max]	9 V, 300 mA
Battery / accumulator type	Alkali(-Manganese)
Battery	6×1.5 V AA
Battery connection	Pad + Spring
Battery operating time - backlight off	25 h
Battery operating time	25 h
Battery capacity	2.900 mAh
Battery voltage	1,5 V

Environmental conditions

Ambient temperature [Min]	10 °C
Ambient temperature [Max]	30 °C
Storage temperature [Min]	-10 °C
Storage temperature [Max]	60 °C

Approval

CE mark	✓
---------	---

Services (optional)

Article number for DAkKS calibration (tensile force)	963-1610
Article number for DAkKS calibration (compressive force)	963-2610
Article number for DAkKS calibration (tensile force/ compressive force)	963-3610
Article number for factory calibration (tensile force)	961-1610
Article number for factory calibration (compressive force)	961-2610

Category

Brand	Sauter
Product category	Force measurement
Product group	Digital force gauge (internal measuring cell)
Product family	FK

Measuring System

Measuring range force [Max] (N)	10 N
Readability force [d] (N)	0,005 N
Measuring head measuring frequency	1000 Hz
Overload protection (% of [Max])	200%
Default unit	N
Number of platforms / channels	1
Tolerance (% of [Max])	0,5%
Directions of force	tension compression

Display

Display type	LCD
Display digit height	18 mm
Screen reversible	✓

Construction

Dimension housing (W×D×H)	195×83×35 mm
Dimensions completely mounted (W×D×H)	195×83×35 mm
Material housing	plastic
Mounting - force application	External thread M8
Load support (tensile force)	Hook

KERN FK 10



Robust, digital force gauge for tensile and compressive force measurements

Article number for factory calibration (tensile force/ compressive force) 961-3610

Packing & Shipping

Delivery time	1 d
Dimensions packaging (W×D×H)	260×250×80 mm
Net weight	0,72 kg
Shipping method	Parcel service
Net weight approx.	0,75 kg
Gross weight approx.	0,90 kg
Shipping weight	1 kg

Pictograms

STANDARD



OPTION

