

Ultimag® Size 5EM

ROTARY Ultimag®

Part Number: 194644-0XX

All catalog products manufactured after April 1, 2006 are RoHS Compliant

Specifications

Dielectric Strength	1000 VRMS (23 awg); 1200 VRMS (24-33 awg)
Recommended Minimum Heat Sink	Maximum watts dissipated by the Ultimag are based on an unrestricted flow of air at 20°C, with the Ultimag mounted on the equivalent of an aluminum plate measuring 7-1/2" square by 1/8" thick (19.1 cm sq. x 0.32 cm)
Thermal Resistance	5.36°C/watt with heatsink; 12.9°C/watt without heatsink
Rotor Inertia	3.085 x 10 ⁻⁶ (kgm ²)
Peak Torque Rating (Tp)	100 oz.in. (0.7 Nm)
Power Input	210 watts (stalled at Tp; 25°C; Pp)
Number of Phases	1
Static Friction (Tf)	1 oz.in. max. (7mNm)
-3dB Closed Loop	66.5 Hz
Maximum Winding	180°C
Number of Poles	6
Weight:	12.8 oz. (363 gms)
Dimensions:	Ø1.937" x 1.25" L max (Ø49.2 mm x 31.75 mm L max) See page B10.



Performance

Maximum Duty Cycle*	100%	50%	25%	10%
K _M (oz-in/√watt)	10.9	9.2	8.2	6.9
Maximum ON Time (sec) when pulsed continuously ¹	∞	40	15	4
Maximum ON Time (sec) for single pulse ²	∞	109	36	10
Typical Energize Time (msec) ³	6.0	5.5	4.5	4.0
Watts (@ 20°C)	21	42	84	210
Ampere Turns (@ 20°C)	621	878	1242	1964

Coil Data

awg (0XX) ⁴	Resistance (@20°C)	# Turns ⁵	VDC (Nom)	VDC (Nom)	VDC (Nom)	VDC (Nom)
23	1.05	128	4.7	6.6	9.4	14.8
24	2.24	213	6.9	9.7	13.7	21.7
25	3.16	240	8.1	11.5	16.3	25.8
26	4.45	270	9.7	13.7	19.3	30.6
27	8.50	404	13.4	18.9	26.7	42.2
28	11.90	452	15.8	22.3	31.6	50.0
29	21.10	630	21.0	29.7	42.1	67.0
30	29.50	705	24.9	35.2	49.8	78.7
31	50.30	948	32.5	45.9	65.0	103.0
32	82.70	1232	41.7	58.9	83.0	132.0
33	134.00	1576	53.0	74.9	106.0	168.0

*Not recommended for full stroke at 100% duty cycle.

How to Order

Add the coil awg number (0XX) to the part number (for example: to order a 25% duty cycle rated at 26.7 VDC, specify 194644-027).

Please see www.ledex.com (click on Stock Products tab) for our list of stock products available through our North American distributors.

¹ Continuously pulsed at stated watts and duty cycle

² Single pulse at stated watts (with coil at ambient room temperature 20°C)

³ Typical energize time based on no load condition. Times shown are for half of full rotary stroke starting at center-off position.



⁴ Other coil awg sizes available — please consult factory

⁵ Reference number of turns


WARNING: Exposed Magnet may affect pacemakers.

In the event a product unit's magnet is exposed due to product disassembly, Pacemaker Wearers should distance themselves 10 feet from exposed magnet.

All specifications subject to change without notice.



NOTE: The Size 5EM Ultimag is not recommended for full stroke operation at 100% duty cycle.




Calculate the inertia of your system, then use this chart to determine Ultimag speed in your application. Inertia determination of simple shapes is shown in most engineering handbooks; complex shapes are calculated in solid modeling software or are measured empirically. This graph represents half of the full rotary stroke starting at the center-off position.

Ultimag® Dimensions


ROTARY Ultimag®

inches (mm)


4EM



5EM



6EM



All specifications subject to change without notice.