

**Data Sheet** 

# 1 ft Coax HD15 VGA to 5 BNC RGBHV Monitor Cable - M/F

Product ID: VGABNCMF1



The VGABNCMF1 1-foot Coax HD15 VGA to 5 BNC RGBHV Adapter Cable features an HD15 VGA (male) connector and 5 BNC (RGBHV) (female) connectors, allowing you to connect your existing BNC video source to a VGA distribution amplifier or PC.

The cable can also be used with a VGA out signal, breaking out to 5 BNC female connectors that can be used with a 5 BNC (M-M) cable for use with a BNC monitor/display.

www.startech.com/uk 0800 169 0408



### **Data Sheet**

#### Certifications, Reports and Compatibility







#### Applications

• Connect your BNC connected cabled panels and projectors to a VGA distribution amplifier or PC

#### Features

- Short flexible cable design
- HD15 VGA Male to 5 BNC Female Connectors

www.startech.com/uk 0800 169 0408



Hard-to-find made easy\*

## **Data Sheet**

|                                 | Warranty                  | Lifetime   |
|---------------------------------|---------------------------|--|
| Hardware                        | Cable Jacket Type         | PVC - Polyvinyl Chloride   |
|                                 | Connector Plating         | Nickel   |
|                                 | Fire Rating               | CMG Rated (General Purpose)  |
| Connector(s)                    | Connector A               | 1 - VGA (15 pin, High Density D-Sub) Male  |
|                                 | Connector B               | 5 - BNC (RF Coax) Female   |
| Special Notes /<br>Requirements | Note                      | RGB signal: Red, Green, Blue wires, Vertical Sync: Black wire, Horizontal Sync: White wire |
| Physical<br>Characteristics     | Cable Length              | 0.3 m [1 ft]   |
|                                 | Cable OD                  | 8.5 mm [0.3 in]  |
|                                 | Color                     | Black  |
|                                 | Product Length            | 0.3 m [1 ft]   |
|                                 | Weight of Product         | 103 g [3.6 oz]   |
|                                 | Wire Gauge                | 28 AWG   |
| Packaging<br>Information        | Package Height            | 17 mm [0.7 in]   |
|                                 | Package Length            | 22.5 cm [8.9 in]   |
|                                 | Package Width             | 12.5 cm [4.9 in]   |
|                                 | Shipping (Package) Weight | 108 g [3.8 oz]   |
| What's in the Box               | Included in Package       | 1 - 1 ft Coax HD15 VGA to 5 BNC RGBHV Monitor Cable -<br>M/F                               |

Product appearance and specifications are subject to change without notice.

www.startech.com/uk 0800 169 0408