


Engineers multigrip pliers

176A "Junior" pliers

176A.CPY : Polished chrome finish, comfortable grips.

	A	B	C	e	H	L	ΔΔ
	mm	mm	mm	mm	mm	mm	g
176A.CPY	23,5	23	40	5.6	45	165	160



"Mammoth" pliers

182A.CP

- Powerful, two-handed use ideal for heavy engineering and farm machinery.
 - Forged and hardened to 48 HRC.
 - Thick-gauge jaws withstand torsion.
 - 7 settings.
 - Chrome finish, polished tips.
 - Capacity 58 mm.
- ΔΔ : 810 g.



	Description
182A.CP	Spare pivot pin

► Twin slip-joint multigrip pliers

484 Twin slip-joint multigrip pliers

- ISO 8976, DIN ISO 8976, NF ISO 8976.
 - Inter-slotted jaws distribute load either side of central pin, in two heavy-gauge slots, for optimum safety and durability.
 - 7 settings.
 - Satin finish.
- 484A : capacity 34 mm.
484A.30, capacity 43 mm.

	e	A	B	C	H	L	ΔΔ
	mm	mm	mm	mm	mm	mm	g
484A	7,0	33	38	60	50	240	345
484A.30	9,5	38	40	66	52	300	560



► Notch-joint multigrip pliers

Notch-joint multigrip pliers

480.ECG

- ISO 8976, DIN ISO 8976, NF ISO 8976.
 - Undercut arcs :
 - Positive engagement of notches provides high power.
 - Pivot pin is not load bearing.
 - Smooth adjustment.
 - 5 settings.
 - Chrome finish, red PVC grips.
- ΔΔ : 320 g.

