

PART OBSOLETE -NO ALTERNATE PART



MMBZ5V6AL - MMBZ33VAL

24W AND 40W PEAK POWER DUAL SURFACE MOUNT TVS

Features


- Dual TVS in Common Anode Configuration
- 24W/40W Peak Power Dissipation Rating @ 1.0ms (Unidirectional)
- 225mW Power Dissipation
- Ideally Suited for Automated Insertion
- Low Leakage
- Totally Lead-Free & Fully RoHS Compliant (Notes 1 & 2)
- Halogen and Antimony Free. "Green" Device (Note 3)
- Qualified to AEC-Q101 Standards for High Reliability

Mechanical Data

- Case: SOT23
- Case Material: Molded Plastic "Green" Molding Compound. UL Flammability Classification 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Solderable per MIL-STD-202, Method 208 (3)
- Polarity: See Diagram
- Lead Free Plating (Matte Tin Finish Annealed over Alloy 42 Leadframe).
- Weight: 0.008 grams (Approximate)



Top View



Device Schematic

Ordering Information (Note 5)


Part Number	Qualification	Case	Packaging
(Type Number)-7*-F	Commercial	SOT23	3,000/Tape & Reel
(Type Number)Q-7*-F (Note 4)	Automotive	SOT23	3,000/Tape & Reel

^{*} Example: 5.6V type = MMBZ5V6AL-7-F.

- 1. No purposely added lead. Fully EU Directive 2002/95/EC (RoHS) & 2011/65/EU (RoHS 2) compliant.
- 2. See http://www.diodes.com for more information about Diodes Incorporated's definitions of Halogen- and Antimony-free, "Green" and Lead-free.

 3. Halogen- and Antimony-free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and
- <1000ppm antimony compounds.
- 4. Automotive products are AEC-Q101 qualified and are PPAP capable. Automotive, AEC-Q101 and standard products are electrically and thermally the same, except where specified. For more information, please refer to https://www.diodes.com/quality/product-compliance-definitions/.
- 5. For packaging details, go to our website at https://www.diodes.com/design/support/packaging/diodes-packaging/.

Marking Information



xxx = Product type marking code, See Electrical Characteristics Table, Pages 2 YM = Date Code Marking Y = Year (ex: I = 2021)M = Month (ex: 9 = September)

Date Code Key

Year	2006	2007	2008	2009	 2018	2019	2020	2021	2022	2023	2024	2025
Code	Т	U	V	W	 F	G	Н	I	J	K	L	М

Month	Jan	Feb	Mar	Apr	May	Jun	Jul	Aug	Sep	Oct	Nov	Dec
Code	1	2	3	4	5	6	7	8	9	0	N	D



Maximum Ratings (@T_A = +25°C, unless otherwise specified.)

Characteristic	Symbol	Value	Unit
Peak Power Dissipation: MMBZ5V6AL - MMBZ10VAL (Note 7)	P_{PK}	24	W
Peak Power Dissipation: MMBZ15VAL - MMBZ33VAL (Note 7)	P _{PK}	40	W

Thermal Characteristics

Characteristic	Symbol	Value	Unit
Power Dissipation (Note 6)	P_{D}	225	mW
Thermal Resistance, Junction to Ambient Air (Note 6)	$R_{\theta JA}$	556	°C/W
Operating and Storage Temperature Range	T _J , T _{STG}	-55 to +150	°C

Electrical Characteristics (@T_A = +25°C, unless otherwise specified.)

24 Watt (V_F = 0.9V max @ I_F = 10mA)

			Max Reverse Breakdown Voltage				Max. Clam V _C @ I _F	Typical Temperature		
Type Number	Marking Code	V _{RWM}	Current, I _R @ V _{RWM} (Note 8)	VE	_{BR} (Note 8)	(y)	@ I _т	Vc	l _{PP}	Coefficient of Reverse Voltage
		Volts	μA	Min	Nom	Max	mA	٧	Α	T _C (mV/°C)
MMBZ5V6AL	K9A	3	5.0	5.32	5.6	5.88	20	8.0	3.0	1.8

24 Watt ($V_F = 0.9V \text{ max } @ I_F = 10\text{mA}$)

			Max Reverse	Rreakdown Voltage		Broakdown Voltago			Typical Temperature	
Type Number	Marking Code	V _{RWM}	Current, I _R @ V _{RWM} (Note 8)	VE	_{BR} (Note 8)	(V)	@ I _T	Vc	l _{PP}	Coefficient of Reverse Voltage
		Volts	μA	Min	Nom	Max	mA	V	Α	T _C (%/°C)
MMBZ6V2AL	K9B	3.0	0.5	5.89	6.2	6.51	1.0	8.7	2.76	+0.04
MMBZ6V8AL	K9C	4.5	0.5	6.46	6.8	7.14	1.0	9.6	2.5	+0.045
MMBZ9V1AL	K9D	6.0	0.3	8.65	9.1	9.56	1.0	14	1.7	+0.065
MMBZ10VAL	K9E	6.5	0.3	9.50	10	10.5	1.0	14.2	1.7	+0.065


40 Watt ($V_F = 0.9V \text{ max } @ I_F = 10\text{mA}$)


			Max. Reverse		Breakdo	wn Voltage			ping Voltage, P (Note 7)	Typical Temperature
Type Number	Marking Code	V _{RWM}	Current, I _R @ V _{RWM} (Note 8)	V _B	_{sR} (Note 8)	(V)	@ I _T	Vc	l _{PP}	Coefficient of Reverse Voltage
		Volts	nA	Min	Nom	Max	mA	V	Α	T _C (%/°C)
MMBZ15VAL	K9K	12	50	14.25	15	15.75	1.0	21	1.9	+0.080
MMBZ18VAL	K9L	14.5	50	17.10	18	18.90	1.0	25	1.6	+0.090
MMBZ20VAL	K9N	17	50	19.00	20	21.00	1.0	28	1.4	+0.090
MMBZ33VAL	K9T	26	50	31.35	33	34.65	1.0	46	0.87	+0.090

Notes: 6. Device mounted on FR-4 PCB pad layout (2oz copper) as shown on Diodes website at http://www.diodes.com/package-outlines.html.


- 7. Non-repetitive current pulse per Figure 2 and derate above $T_A = +25^{\circ}C$ per Figure 2.
- 8. Short duration pulse test used to minimize self-heating effect.







BIAS (V)
Fig. 3 Typical Capacitance vs. Bias Voltage (Lower curve is Bidirectional mode, Upper curve is Unidirectional mode)









Fig. 4 Typical Capacitance vs. Bias Voltage (Lower curve is Bidirectional mode, Upper curve is Unidirectional mode)










for voltage classification



Package Outline Dimensions

Please see http://www.diodes.com/package-outlines.html for the latest version.

SOT23




	SOT23									
Dim	Min	Max	Тур							
Α	0.37	0.51	0.40							
В	1.20	1.40	1.30							
С	2.30	2.50	2.40							
D	0.89	1.03	0.915							
F	0.45	0.60	0.535							
G	1.78	2.05	1.83							
Н	2.80	3.00	2.90							
J	0.013	0.10	0.05							
K	0.890	1.00	0.975							
K1	0.903	1.10	1.025							
L	0.45	0.61	0.55							
L1	0.25	0.55	0.40							
М	0.085	0.150	0.110							
а	0°	8°								
All	Dimens	ions in	mm							

Suggested Pad Layout

Please see http://www.diodes.com/package-outlines.html for the latest version.

SOT23



Dimensions	Value (in mm)
С	2.0
Х	0.8
X1	1.35
Y	0.9
V4	0.0



IMPORTANT NOTICE

- 1. DIODES INCORPORATED AND ITS SUBSIDIARIES ("DIODES") MAKE NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO ANY INFORMATION CONTAINED IN THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO, THE IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR NON-INFRINGEMENT OF THIRD PARTY INTELLECTUAL PROPERTY RIGHTS (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).
- 2. The Information contained herein is for informational purpose only and is provided only to illustrate the operation of Diodes products described herein and application examples. Diodes does not assume any liability arising out of the application or use of this document or any product described herein. This document is intended for skilled and technically trained engineering customers and users who design with Diodes products. Diodes products may be used to facilitate safety-related applications; however, in all instances customers and users are responsible for (a) selecting the appropriate Diodes products for their applications, (b) evaluating the suitability of the Diodes products for their intended applications, (c) ensuring their applications, which incorporate Diodes products, comply the applicable legal and regulatory requirements as well as safety and functional-safety related standards, and (d) ensuring they design with appropriate safeguards (including testing, validation, quality control techniques, redundancy, malfunction prevention, and appropriate treatment for aging degradation) to minimize the risks associated with their applications.
- 3. Diodes assumes no liability for any application-related information, support, assistance or feedback that may be provided by Diodes from time to time. Any customer or user of this document or products described herein will assume all risks and liabilities associated with such use, and will hold Diodes and all companies whose products are represented herein or on Diodes' websites, harmless against all damages and liabilities.
- 4. Products described herein may be covered by one or more United States, international or foreign patents and pending patent applications. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks and trademark applications. Diodes does not convey any license under any of its intellectual property rights or the rights of any third parties (including third parties whose products and services may be described in this document or on Diodes' website) under this document.
- 5. Diodes products are provided subject to Diodes' Standard Terms and Conditions of Sale (https://www.diodes.com/about/company/terms-and-conditions/terms-and-conditions-of-sales/) or other applicable terms. This document does not alter or expand the applicable warranties provided by Diodes. Diodes does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel.
- 6. Diodes products and technology may not be used for or incorporated into any products or systems whose manufacture, use or sale is prohibited under any applicable laws and regulations. Should customers or users use Diodes products in contravention of any applicable laws or regulations, or for any unintended or unauthorized application, customers and users will (a) be solely responsible for any damages, losses or penalties arising in connection therewith or as a result thereof, and (b) indemnify and hold Diodes and its representatives and agents harmless against any and all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim relating to any noncompliance with the applicable laws and regulations, as well as any unintended or unauthorized application.
- 7. While efforts have been made to ensure the information contained in this document is accurate, complete and current, it may contain technical inaccuracies, omissions and typographical errors. Diodes does not warrant that information contained in this document is error-free and Diodes is under no obligation to update or otherwise correct this information. Notwithstanding the foregoing, Diodes reserves the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. This document is written in English but may be translated into multiple languages for reference. Only the English version of this document is the final and determinative format released by Diodes.
- 8. Any unauthorized copying, modification, distribution, transmission, display or other use of this document (or any portion hereof) is prohibited. Diodes assumes no responsibility for any losses incurred by the customers or users or any third parties arising from any such unauthorized use.

Copyright © 2021 Diodes Incorporated

www.diodes.com