




SFP28

TE Internal #: 1-2007562-7

SFP+, Cage Assembly with Integrated Connector, .8mm [.032in]  
Centerline, Signal, Operating Temperature Range -55 – 105 °C [-67 – 221 °F]

[View on TE.com >](#)

Connectors > Pluggable IO Connectors & Cages > SFP+ Stacked Cage Assemblies



Form Factor: **SFP+**  
Pluggable I/O Product Type: **Cage Assembly with Integrated Connector**  
Centerline (Pitch): **.8 mm [ .032 in ]**  
Sealable: **No**  
Circuit Application: **Signal**

[All SFP+ Stacked Cage Assemblies \(73\)](#)

Features

Product Type Features

|                            |                                         |
|----------------------------|-----------------------------------------|
| Cage Type                  | Stacked                                 |
| Form Factor                | SFP+                                    |
| Pluggable I/O Product Type | Cage Assembly with Integrated Connector |
| Sealable                   | No                                      |

Configuration Features

|                           |       |
|---------------------------|-------|
| Number of Positions       | 240   |
| Number of Ports           | 12    |
| Port Matrix Configuration | 2 x 6 |

Electrical Characteristics

|                 |         |
|-----------------|---------|
| Data Rate (Max) | 16 Gb/s |
|-----------------|---------|

Contact Features

|                                      |                                          |
|--------------------------------------|------------------------------------------|
| Contact Mating Area Plating Material | Gold or Gold Flash over Palladium Nickel |
|--------------------------------------|------------------------------------------|



|                                                |        |
|------------------------------------------------|--------|
| Tail Plating Material                          | Tin    |
| Contact Mating Area Plating Material Thickness | .76 µm |

Termination Features

|                                |                          |
|--------------------------------|--------------------------|
| Termination Method to PCB      | Through Hole - Press-Fit |
| Termination Post & Tail Length | 3 mm[.118 in]            |

Housing Features

|                    |                |
|--------------------|----------------|
| Cage Material      | Nickel Silver  |
| Centerline (Pitch) | .8 mm[.032 in] |

Dimensions

|                             |                 |
|-----------------------------|-----------------|
| PCB Thickness (Recommended) | 1.5 mm[.059 in] |
|-----------------------------|-----------------|

Usage Conditions

|                             |                            |
|-----------------------------|----------------------------|
| Operating Temperature Range | -55 – 105 °C[-67 – 221 °F] |
|-----------------------------|----------------------------|

Operation/Application

|                            |              |
|----------------------------|--------------|
| Pluggable I/O Applications | EMI Enhanced |
| Heat Sink Compatible       | No           |
| Circuit Application        | Signal       |

Industry Standards

|                        |          |
|------------------------|----------|
| UL Flammability Rating | UL 94V-0 |
|------------------------|----------|

Packaging Features

|                  |         |
|------------------|---------|
| Packaging Method | Package |
|------------------|---------|

Other

|                              |                               |
|------------------------------|-------------------------------|
| Included Lightpipe           | Yes                           |
| EMI Containment Feature Type | Internal/External EMI Springs |

Product Compliance

For compliance documentation, visit the product page on TE.com>

|                                               |                                                                                                |
|-----------------------------------------------|------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU                  | Compliant                                                                                      |
| EU ELV Directive 2000/53/EC                   | Compliant                                                                                      |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold                                                        |
| EU REACH Regulation (EC) No. 1907/2006        | Current ECHA Candidate List: JAN 2025 (247)<br>Candidate List Declared Against: JAN 2025 (247) |



|                           |                                                |
|---------------------------|------------------------------------------------|
|                           | Does not contain REACH SVHC                    |
| Halogen Content           | Not Low Halogen - contains Br or Cl > 900 ppm. |
| Solder Process Capability | Not applicable for solder process capability   |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

|                                                                                                                                                             |                                                                                                                                                                  |                                                                                                                                                                     |                                                                                                                                                                    |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|  <p>TE Part # 2821033-8<br/>QSFP TO [4]SFP+, 28G, 1M, 33AWG</p>          |  <p>TE Part # 2142970-6<br/>CABLE ASSY, MICRO SFP+ TO STD SFP+, 5M</p>       |  <p>TE Part # 2142970-5<br/>CABLE ASSY, MICRO SFP+ TO STD SFP+, 4M</p>         |  <p>TE Part # CAT-C11-H506<br/>SFP+ to SFP+ I/O Cable Assembly: 26 AWG</p>    |
|  <p>TE Part # CAT-C11-H5<br/>SFP+ to SFP+ I/O Cable Assembly: 24 AWG</p> |  <p>TE Part # CAT-C11-H50626<br/>SFP+ to SFP+ I/O Cable Assembly: 30 AWG</p> |  <p>TE Part # 2142970-1<br/>CABLE ASSY, MICRO SFP+ TO STD SFP+, 0.5M</p>       |  <p>TE Part # 4-2334985-2<br/>SFP56 DIRECT ATTACH CA, 1M, 32AWG</p>           |
|  <p>TE Part # 2007174-3<br/>SFP 1x6 Light Pipe Assy, Reduced Length</p>  |  <p>TE Part # 2142970-3<br/>CABLE ASSY, MICRO SFP+ TO STD SFP+, 2M</p>       |  <p>TE Part # CAT-Q17-N490333<br/>QSFP56-Four SFP56 Cable Assembly: 26 AWG</p> |  <p>TE Part # CAT-C11-N490333<br/>QSFP28-Four SFP+ Cable Assembly: 30 AWG</p> |



TE Part # CAT-C11-N490325  
QSFP28-Four SFP+ Cable Assembly:  
26 AWG



TE Part # 2007174-1  
SFP Standard 1x6 Light Pipe Assm



TE Part # 2110743-1  
SFP 1x6 Light Pipe Assy, Low Profile



TE Part # CAT-C11-N4901114  
SFP28 to SFP28 Cable Assembly: 30  
AWG



TE Part # 2142970-7  
CABLE ASSY, MICRO SFP+ TO STD  
SFP+, 6M



TE Part # 4-2821222-5  
SFP56 DIRECT ATTACH CA, 2M,  
30AWG



TE Part # 2007174-2  
SFP 1x6 Light Pipe Assy, Reduced  
Length




TE Part # CAT-C11-H5062  
SFP+ to SFP+ I/O Cable Assembly: 28  
AWG

Customers Also Bought



TE Part #CAT-AM71-CH8172  
AMP SUPERSEAL 1.5MM,  
CONNECTOR HOUSING



TE Part #281934-2  
SINGLE WIRE SEAL



TE Part #CAT-D48-ST273  
DEUTSCH Solid Contacts



TE Part #DT04-2P  
REC, 2P, GRY, N



TE Part #DT06-2S  
PLG, 2P, GRY, N



TE Part #CAT-D487-W416  
Wedgelocks: DEUTSCH DT

Documents

Product Drawings

SFP+assy 2x6 EMI Spg Outer LP Sn Enhance

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_1-2007562-7\_E1.2d\_dxf.zip



English

Customer View Model

[ENG\\_CVM\\_CVM\\_1-2007562-7\\_E1.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_1-2007562-7\\_E1.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[4-1773455-3 - Quick Reference Guide SFP+ Solutions](#)

English

Product Specifications

[Application Specification](#)

English

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

[Instruction Sheet \(U.S.\)](#)

English