



Terminals & Splices > Foil Terminals



Accepts Foil Thickness (Max): **.4 mm [.016 in]**

Terminal Plating Material: **Tin**

Packaging Method: **Box**

Features

Contact Features

Terminal Plating Material	Tin
---------------------------	-----

Termination Features

Accepts Foil Thickness (Max)	.4 mm[.016 in]
------------------------------	----------------

Usage Conditions

Insulation Option	Uninsulated
-------------------	-------------

Packaging Features

Packaging Quantity	500
Packaging Method	Box

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247)



Candidate List Declared Against: JAN 2025
(247)
Does not contain REACH SVHC

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



REPRESENTATION ONLY

TE Part # 68026
DAHT TERMI-FOIL ASSY

Also in the Series | TERMI-FOIL




Foil Terminals(23)

Customers Also Bought




TE Part #1-1623933-2
CFR50 5% 390R



TE Part #53245-6
TERMINAL,PG SPR SPD 16-14 10



TE Part #1624364-2
NTC0805 5% 4K7



TE Part #290207-000
202K132-25-00/225-0



TE Part #1879071-1
THS50 R01 5%




TE Part #5-6450860-0
MBXLE VERT RCPT
3HDP+1LP+24S+1LP+3HDP




TE Part #1634201-5
PRFDB1-16F-BG000



TE Part #6116522-3
INV MJ,1X2,PNL GRD,SHLD



TE Part #611198-2
RECEPT,PIDG FASTON 12-10 250



TE Part #281742-5
HEADER HE14 RA 2X5 P

Documents

Product Drawings

[SPLICE,TERMI-FOIL BOND CLIP](#)

English

CAD Files

Customer View Model

[ENG_CVM_1-332006-0_C.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_1-332006-0_C.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_1-332006-0_C.2d_dxf.zip](#)

English

[3D PDF](#)

English

[3D PDF](#)

3D



Customer View Model

[ENG_CVM_CVM_1-332006-0_H.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-332006-0_H.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_1-332006-0_H.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.