



DRAWING FOR REFERENCE: This is subject to change without notice  
05/31/2013






RECOMMENDED PCB LAYOUT  
(MOUNTING SURFACE SIDE) (FREE)




RECOMMENDED METAL MASK (FREE)

THICKNESS : 0.1mm  
OPEN AREA RATIO:100%




MATING FIGURE(5:1)



- NOTES 1. LEAD CO-PLANARITY SHALL BE 0.1mm MAX  
2. PLEASE CONSULT HIROSE WHEN THE PRODUCT IS MOUNTED TO FPC.

A (10 : 1)




3	BRASS	CONTACT AREA : Sn PLATING 1μm MIN UNDER PLATING : Cu PLATING 0.3μm MIN	6	PS	REEL , BLACK
2	BRASS	CONTACT AREA : Au PLATING 0.05μm MIN LEAD AREA : Au PLATING 0.05μm MIN UNDER PLATING : Ni PLATING 1μm MIN	5	POLYESTER	CLEAR
1	LCP	BLACK , UL94V-0	4	PS	CLEAR
NO.	MATERIAL	FINISH , REMARKS	NO.	MATERIAL	CLEAR

UNITS mm		SCALE 5 : 1	COUNT △	DESCRIPTION OF REVISIONS	DESIGNED	CHECKED	DATE
APPROVED : KI. AKIYAMA		12.07.02		DRAWING NO.		EDC3-337107-01	
CHECKED : HK. UMEHARA		12.07.02		PART NO.		DF50A-5P-1H(51)	
DESIGNED : ST. SATO		12.06.29		CODE NO.		CL665-1034-2-51	
DRAWN : MI. SAKIMURA		12.06.28				△ 1/2	

DRAWING FOR REFERENCE: This is subject to change without notice  
05/31/2013



<b>HRS</b>	DRAWING NO.	EDC3-337107-01
	PART NO.	DF50A-5P-1H(51)
	CODE NO.	CL665-1034-2-51
		$\triangle$ 2/2