

## Electronic housing - EMG 30-LG - 2947860

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Electronic housing, with snap foot for DIN rail EN 50022 for PCB insertion, without screw connection terminal blocks and cover

### Why buy this product

- ✓ Choice of four cover sizes in transparent or color versions
- ✓ Practical and easy-to-wire conductor connections
- ✓ Space-saving accommodation of electronic components in finely graded module versions available with 10 to 150 mm pitch
- ✓ Uniform and appropriate housing technology
- ✓ High degree of flexibility due to the wide choice of versions
- ✓ User-friendly and safe mounting on DIN rails according to EN 60715
- ✓ Inflammability class V0 insulation material (according to UL 94)
- ✓ Shock and contamination-proof accommodation of electronic components
- ✓ Universal PCBs for all pitches
- ✓



### Key commercial data

Packing unit	5 pc
Minimum order quantity	5 pc
GTIN	 4 017918 082970
Weight per Piece (excluding packing)	31.74 g
Custom tariff number	85472000
Country of origin	Germany

### Technical data

Product type	Component housing lower part
Approval	EAC
Width	30 mm
Height	47.5 mm
Depth	75 mm
Color	green

# Electronic housing - EMG 30-LG - 2947860

## Technical data

No. of pos. for cross connection	-
Type of cross connection	without bus connector
Functional earth ground contact	without

## Classifications

### eCl@ss

eCl@ss 4.0	27180401
eCl@ss 4.1	27180401
eCl@ss 5.0	27180506
eCl@ss 5.1	27180506
eCl@ss 6.0	27180802
eCl@ss 7.0	27182702
eCl@ss 8.0	27182702

### ETIM

ETIM 2.0	EC001031
ETIM 3.0	EC001031
ETIM 4.0	EC001031
ETIM 5.0	EC001031

### UNSPSC

UNSPSC 6.01	31261501
UNSPSC 7.0901	31261501
UNSPSC 11	31261501
UNSPSC 12.01	31261501
UNSPSC 13.2	31261501

## Approvals

### Approvals

---

Approvals

EAC

---

Ex Approvals

---

Approvals submitted

---

### Approval details

## Electronic housing - EMG 30-LG - 2947860

### Approvals

EAC

### Accessories

Accessories

Device marking

Marking material - EMG-GKS 22 - 2941594



Equipment marker tag, width 22 mm

Marking material - EMG-GKS 22 - 2941594



Equipment marker tag, width 22 mm

### PCB

Electronic housing - P 1-EMG 30 - 2947912



PCB for assembling electronic components

Marking material - EMG-GKS 12 - 2947035



Equipment marker, width 12 mm

## Electronic housing - EMG 30-LG - 2947860

### Accessories

Marking material - EMG-SGKS 10 - 2947585



Equipment marker, narrow

---

Marking material - EMG-SGKS 10 - 2947585



Equipment marker, narrow

---

Marking material - EMG-GKS 12 - 2947035



Equipment marker, width 12 mm

---

### Necessary add-on products

Electronic housing - EMG 30-H 7,5MM KLAR - 2947886



Covering hood, for the contact and dust-protected encapsulation of the components, in transparent design. Height: 7.5 mm, width: 30 mm

---

Electronic housing - EMG 30-H 15MM KLAR - 2947899



Covering hood, for the contact and dust-protected encapsulation of the components, in transparent design. Height: 15 mm, width: 30 mm

---

# Electronic housing - EMG 30-LG - 2947860

## Accessories


Electronic housing - EMG 30-H 52MM GN - 2947909



Covering hood, for the contact and dust-protected encapsulation of the components, in green design. Height: 52 mm, width: 30 mm


## Drawings

Dimensional drawing



1 = Top edge of the PCB  
B = Housing width

Dimensional drawing



Pitch 5 mm  
a = Area for mounting components, 38 mm in the hood  
b = Area for mounting components, 45 mm in the housing