

PINCERS 1000V

EGA Master insulated tools comply with IEC 60900 international standard, each one of the pieces being tested at 10,000V (10 times the voltage we certify). They are also tested rigorously according to what the norms establishes: adherence test, impact test, flame propagation test and dielectric penetration test.



 **1.000V**
IEC 60900



MAIN APPLICATION FIELDS

| | | |
|-----------------------------------|-----------------------|----------------------------------|
| Electrical installation | High Voltage networks | Electric maintenance |
| Power Plants | Low Voltage networks | Fire-fighters |
| Electric Stations and substations | Telecommunications | Lighting installation and repair |

CAUTION

- 1 Don't ever use tools under voltage if they present pores, fissures, encrusted elements or if the white insulation layer is visible.
- 2 Insulating floors and safety shoes are recommended to work under voltage.
- 3 Avoid contact with water while working under voltage.
- 4 Do not ever touch directly any item that may be under voltage. Use a voltage tester to check first.

PINCERS 1000V

EGA Master manufactures a wide range of 1000V insulated pliers, box joints, groove joints, cable cutters...**They are designed for the most demanding professionals.**



 **1.000V**
IEC 60900




1. An extraordinary grip allows a firm holding a variety of materials with only one hand.

2. PVC insulation provides maximum adherence and safety against possible contingencies.

3. Anti-shock guards and ends.

4. Un-erasable laser marking.

BOX JOINT

| COD. | L (inch) |  |  |  |
|--------------|----------|---|---|--|
| 73004 | 10 | 450 | 6 | • |
| 73005 | 12 | 600 | | |




 **1000V** | IEC 60900



TECHNICAL SPECIFICATIONS

| | | |
|----------|-----------|-----------|
| MATERIAL | Cr-V | |
| | Handles | PVC |
| HARDNESS | General | 40-48 HRc |
| | Teeth | 42-50 HRc |
| | Pin | 28-50 HRc |
| FINISH | Titacrom® | |
| | Handles | Orange |

GROOVE JOINT

| COD. | L (inch) |  |  |  |
|--------------|----------|---|---|--|
| 73001 | 10 | 450 | 6 | • |
| 73012 | 12 | 720 | | |





 1000V | IEC 60900



TECHNICAL SPECIFICATIONS

| | | |
|----------|---------------|-----------|
| MATERIAL | Special steel | |
| | Handles | PVC |
| HARDNESS | General | 45-50 HRc |
| | Screw | 28-50 HRc |
| FINISH | Titacrom® | |
| | Handles | Orange |

CABLE CUTTERS





| COD. | L (mm) | L (inch) |  | Cu/Al (mm2) |  |  |  |
|--------------|--------|----------|--|-------------|--|--|--|
| 76147 | 150 | 6 | 6,7 | 35 | 180 | 6 | • |

 1000V | IEC 60900



TECHNICAL SPECIFICATIONS

| | | |
|----------|---------------|-----------|
| MATERIAL | Steel | |
| | Handles | PVC |
| HARDNESS | General | 42-48 HRc |
| | Cutting edges | 55-60 HRc |
| FINISH | Handles | Orange |


| COD. | L (mm) | L (inch) |  | Cu/Al (mm2) |  |  |  |
|--------------|--------|----------|---|-------------|---|---|---|
| 73008 | 250 | 10 | 9 | 63 | 500 | 6 | • |




 1000V | IEC 60900



TECHNICAL SPECIFICATIONS

| | | |
|----------|---------------|--------|
| MATERIAL | Special steel | |
| | Handles | PVC |
| HARDNESS | Cutting edges | 45 HRc |
| | Handles | Orange |



| COD. | L (mm) | L (inch) |  | A (mm) | Cu/Al (mm2) | B (mm) | C (mm) |  |  |
|--------------|--------|----------|---|--------|-------------|--------|--------|--|---|
| 73009 | 600 | 24 | 14 | 70 | 154 | 16 | 55 | 1850 | 1 |

 1000V | IEC 60900



TECHNICAL SPECIFICATIONS

| | | |
|----------|---------------|-----------|
| MATERIAL | Special steel | |
| | Handles | PVC |
| HARDNESS | Cutting edges | 54-58 HRc |
| | Handles | Orange |