

High performance sealed 3/4" ratchet



Standards:

NF ISO 3315, ISO 3315, DIN 3122, ASME B107.10

Description:

- Very long durability regardless of working conditions. Maintenance-free. Mechanism sealed to industrial dust.
- 120 tooth mechanism for 3° increments.
- Lever reversing: easy even when wearing gloves. Visible rotation direction.
- "Palm control" system, to press the ratchet head when tightening or loosening without risk of accidental reversing of the rotation direction.
- Ultra-compact head.
- Bi-material elastomer grip: high resistance to abrasion and the most severe workshop solvents: SP95, SP98, diesel fuel, acetone, brake fluid, Skydrol, Jet Oil, kerosene.
- Hole in the handle for strapping when working in high places.
- Finish: mat chrome.

	Diameter [mm]	Diameter D1 [mm]	Length L [mm]	Length L1 [mm]	Height H [mm]	Weight [Kg]
KL.161PB	60.0	31/35	512.0	481.0	52.0	1.47