

Metal drill bits HSS PointTeQ

PRODUCT PROPERTIES					ORDERING INFORMATION				
Diameter (D) mm	Working length mm	Total length mm	Shank diameter (d) mm	Diameter (D) Inch	Packaging type	Pack quantity	Minimum order quantity	Barcode	Part number
5	52	86	5	-	PC1d	1	5	3165140906746	2 608 577 165
5.5	57	93	5.5	-	PC1d	1	5	3165140906753	2 608 577 166
6	57	93	6	-	PC1d	1	5	3165140906760	2 608 577 167
6.5	63	101	6.5	-	PC1d	1	5	3165140906777	2 608 577 168
7	69	109	7	-	PC1d	1	5	3165140906784	2 608 577 169
7.5	69	109	7.5	-	PC1d	1	5	3165140906791	2 608 577 170
8	75	117	8	-	PC1d	1	5	3165140906807	2 608 577 171
8.5	75	117	8.5	-	PC1d	1	5	3165140906814	2 608 577 172
9	81	125	9	-	PC1d	1	5	3165140906821	2 608 577 173
10	87	133	10	-	PC1d	1	5	3165140906838	2 608 577 174
11	94	142	11	-	PC1d	1	5	3165140906845	2 608 577 175
12	101	151	12	-	PC1d	1	5	3165140906852	2 608 577 176
13	101	151	13	-	PC1d	1	5	3165140906869	2 608 577 177

Pack of 10

1	12	34	1	-	P2a	10	1	3165140906876	2 608 577 178
1.1	14	36	1.1	-	P2a	10	1	3165140906883	2 608 577 179
1.2	16	38	1.2	-	P2a	10	1	3165140906890	2 608 577 180
1.3	16	38	1.3	-	P2a	10	1	3165140906906	2 608 577 181
1.4	18	40	1.4	-	P2a	10	1	3165140906913	2 608 577 182
1.5	18	40	1.5	-	P2a	10	1	3165140906920	2 608 577 183
1.6	20	43	1.6	-	P2a	10	1	3165140906937	2 608 577 184
1.7	20	43	1.7	-	P2a	10	1	3165140906944	2 608 577 185
1.8	22	46	1.8	-	P2a	10	1	3165140906951	2 608 577 186
1.9	22	46	1.9	-	P2a	10	1	3165140906968	2 608 577 187
2	24	49	2	-	P2a	10	1	3165140906975	2 608 577 188
2.1	24	49	2.1	-	P2a	10	1	3165140906982	2 608 577 189
2.2	27	53	2.2	-	P2a	10	1	3165140906999	2 608 577 190
2.3	27	53	2.3	-	P2a	10	1	3165140907002	2 608 577 191
2.4	30	57	2.4	-	P2a	10	1	3165140907019	2 608 577 192
2.5	30	57	2.5	-	P2a	10	1	3165140907026	2 608 577 193
2.6	30	57	2.6	-	P2a	10	1	3165140907033	2 608 577 194
2.7	33	61	2.7	-	P2a	10	1	3165140907040	2 608 577 195
2.8	33	61	2.8	-	P2a	10	1	3165140907057	2 608 577 196
2.9	33	61	2.9	-	P2a	10	1	3165140907064	2 608 577 197
3	33	61	3	-	P2a	10	1	3165140907071	2 608 577 198
3.1	36	65	3.1	-	P2a	10	1	3165140907088	2 608 577 199
3.2	36	65	3.2	-	P2a	10	1	3165140907095	2 608 577 200
3.3	36	65	3.3	-	P2a	10	1	3165140907101	2 608 577 201
3.4	39	70	3.4	-	P2a	10	1	3165140907118	2 608 577 202
3.5	39	70	3.5	-	P2a	10	1	3165140907125	2 608 577 203
3.6	39	70	3.6	-	P2a	10	1	3165140907132	2 608 577 204
3.7	39	70	3.7	-	P2a	10	1	3165140907149	2 608 577 205
3.8	43	75	3.8	-	P2a	10	1	3165140907156	2 608 577 206
3.9	43	75	3.9	-	P2a	10	1	3165140907163	2 608 577 207
4	43	75	4	-	P1h	10	1	3165140907170	2 608 577 208
4.1	43	75	4.1	-	P1h	10	1	3165140907187	2 608 577 209
4.2	43	75	4.2	-	P1h	10	1	3165140907194	2 608 577 210
4.3	47	80	4.3	-	P1h	10	1	3165140907200	2 608 577 211
4.4	47	80	4.4	-	P1h	10	1	3165140907217	2 608 577 212
4.5	47	80	4.5	-	P1h	10	1	3165140907224	2 608 577 213
4.6	47	80	4.6	-	P1h	10	1	3165140907231	2 608 577 214
4.7	47	80	4.7	-	P1h	10	1	3165140907248	2 608 577 215
4.8	52	86	4.8	-	P1h	10	1	3165140907255	2 608 577 216
4.9	52	86	4.9	-	P1h	10	1	3165140907262	2 608 577 217
5	52	86	5	-	P1h	10	1	3165140907279	2 608 577 218