


FEATURES

- **Annealed Copper Conductor:** Provides superior electrical conductivity and flexibility
- **Polyvinyl Chloride Jacket:** Offers protection against environmental factors and mechanical stress
- **Plain Conductor Type:** Ensures consistent performance and ease of installation
- **24/0.2 Core Strands:** Enhances flexibility and durability for dynamic applications
- **Temperature Range -15 °C to 70 °C:** Suitable for a variety of environmental conditions
- **Voltage Rating of 500 V:** Supports a wide range of electrical applications
- **White Jacket Colour:** Allows for easy identification and aesthetic integration

RS PRO 0.75 mm² Flexible Cable, 50 m Length

RS Stock No: 606-135



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO flexible cable is designed for a wide range of industrial and commercial applications. With a conductor made from annealed copper, it ensures excellent conductivity and reliability. The cable is ideal for installations requiring flexibility and durability, making it suitable for various electrical setups.

General Specifications

Conductor Material	Annealed Copper
Conductor Type	Plain
Jacket Colour	White
Product Type	Flexible Cable

Mechanical Specifications

Cable CSA	0.75 mm ²
Cable Length	50 m
Core Strands	24/0.2
Jacket Material	Polyvinyl Chloride
Number of Cores	3
Outside Diameter	7.6 mm

Operation Environment Specifications

Maximum Operating Temperature	70 °C
Minimum Operating Temperature	-15 °C

Approvals

Standards/Approvals	ACI, BASEC ISO 9001 UKAS CS1-029, BS EN 50363-3, BS EN 50363-4-1, BS EN 50525-2-11, BS EN 60228
---------------------	-------------------------------------------------------------------------------------------------

Electrical Specifications

Voltage	500 V
---------	-------