

Brush Cutter XGT®

UR012G

40Vmax X2 • 0 - 6 800 / 0 - 5 000 /
0 - 3 500 min⁻¹

Powerful XGT® 40Vmax X2 Grass trimmer with Bike handle for various applications.

UR012G has a brushless motor and 3 - speed (Low/ Medium/High) motor system. Reverse rotation system allows operator to quickly clear trimmer head / blade of entangled grass and weeds. Soft start feature for added motor protection.



XGT 80Vmax **BL** MOTOR **ADT** **AFT**

Technical specifications

Voltage XGT	✓
Nominal Battery Voltage	2 x 40 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
No load speed	0 - 3500 / 5000 / 6800 min ⁻¹
Cutting width	225 / 255 / 270 / 305 / 480 mm
Spindle Thread	M10 x 1,25 LH
Handle Type	U
Sound Power Level (L _{WA})	96,2 - 97,7 dB(A)
Sound Pressure Level (L _{pA})	79,9 - 84,3 dB(A)
Noise Uncertainty (K Factor)	0,6 - 2,1 dB(A)
Product net weight	6,3 kg
Tool weight with battery	8,0 - 10,5 kg
Product Dimensions (L x W x H):	1790 x 680 x 590 mm

User benefits

- 3-speed options (Low / Medium / High) allows the operator to match speed to application
- Active Feedback sensing Technology (AFT) stops the engine if the rotation suddenly stops
- Soft start feature for added motor protection
- ADT (Automatic torque Drive Technology) adjusts speed and torque during operation for optimum performance
- Battery protection circuit protects against overloading, over-discharging and over-heating

Link to product - www.makita.uk.com



Related products

■ **Optional AC**

195624-6

2-Tooth Cutting Blade



■ **Other**

User manual

Parts drawing