



# SEAL-D®



## Designed for IP Performance

SEAL-D® I/O Connectors utilize a proprietary sealing technology which maintains the same physical size and footprint as standard D-Sub products. This reduces space on new designs & eliminates the need to redesign enclosures and PC boards when implementing IP66/IP67 design upgrades.



### FEATURES & BENEFITS

- Signal / Low Power in 6 standard sizes:  
(Standard: 9, 15, 25 | High Density: 15, 26, 44)
- Combo-D / High Power in a variety of configurations:  
(3W3, 5W1, 5W5, 7W2, 9W4, 11W1, 13W3, 13W6, 17W2, 21W1, 21WA4)
- Solder Cup, Vertical Mount, & Right Angle Board Mount Options
- High Reliability Screw Machined Contacts
- 3 amp / 5 amp / 20 amp / 40 amp Power Options
- -55C to +105C Operating Temperature Range
- 100% IP Compliant Guaranteed | Made in U.S.A.

[http:// www.norcomp.net](http://www.norcomp.net)

# NORCOMP



### STANDARD IP67

Cable Mount  
Vertical PCB  
Right Angle (0.283" Footprint)  
Right Angle (0.370" Footprint)

### SERIES

772-EYY-Y03RYY1  
772-EYY-Y13RYY1  
773-EYY-Y13RYY1  
774-EYY-Y13RYY1

### SIZE

9 / 15 / 25 Position  
9 / 15 / 25 Position  
9 / 15 / 25 Position  
9 / 15 / 25 Position

### HIGH DENSITY IP67

Cable Mount  
Vertical PCB  
Right Angle

### SERIES

780-MYY-Y03LYY1  
780-MYY-Y13RYY1  
781-MYY-113RYY1

### SIZE

15 / 26 / 44 Position  
15 / 26 / 44 Position  
15 / 26 / 44 Position

NEW

### POWER-D IP67

Cable Mount  
Vertical PCB  
Right Angle

### SERIES

680SYWYY03LY01  
681SYWYY03L001  
684SYWY103L461

### SIZE

3W3 / 5W1 / 5W5 / 7W2  
9W4 / 11W1 / 13W3 / 13W6  
17W2 / 21W1 / 21WA4

### STANDARD IP66

Cable Mount  
Vertical PCB  
Right Angle (0.318" Footprint)  
Right Angle (0.590" Footprint)

### SERIES

671-YYY-103LYY1  
671-YYY-113RYY1  
682-YYY-113RYY1  
683-YYY-113RYY1

### SIZE

9 / 15 / 25 Position  
9 / 15 / 25 Position  
9 / 15 / 25 Position  
9 / 15 / 25 Position

### HIGH DENSITY IP66


Cable Mount  
Vertical PCB  
Vertical PCB (Low Profile)  
Right Angle

### SERIES

680-YYY-103LYY1  
680-YYY-113RYY1  
695-YYY-113LYY1  
681-YYY-113RYY1

### SIZE

15 / 26 / 44 Position  
15 / 26 / 44 Position  
15 / 26 / 44 Position  
15 / 26 / 44 Position



Premium  
IP Rated  
Connectors

