

Product datasheet

Specifications



VarPlus Can HDuty Capacitor - 10.4/12.5 kvar - 480 V - 50/60Hz

Local distributor code:

408307460

BLRCH104A125B48

EAN Code: 3606485255774

Main

Range	PowerLogic
Range of product	PowerLogic
Product or component type	Heavy duty capacitor
Product name	PowerLogic PFC Capacitor
Network frequency	50/60 Hz
Series name	HDuty
Network harmonic content	$\leq 20\%$
Electrical parameters	10.4 kvar 480 V 50 Hz 12.5 kvar 480 V 60 Hz
Maximum permissible voltage	$1.1 \times U_n$ (8 hours over 24 hours)
continuous overcurrent capacity	$1.8 \times I_n$
Rated voltage	480 V AC 50/60 Hz

Complementary

Dielectric losses	$< 0.2 \text{ W/kvar}$
Power losses	$< 0.5 \text{ W/kVAr}$
Capacitance tolerance	- 5 % to 10 %
Voltage test	$2.15 \times U_n$ AC between terminals for 10 s $\leq 660 \text{ V} - 3 \text{ kV}$ AC between terminal and container for 10 s $\geq 660 \text{ V} - 6 \text{ kV}$ AC between terminal and container for 10 s
Inrush current	$250 \times I_n$
Maximum switching operation per year	7000
Service life in hours	130000 h
Dielectric material	Metallized polypropylene film with Zn/Al alloy, special resistivity & profile, special edge (wave cut)
Impregnation material	Non-PCB dry PUR resin Biodegradable
Type of installation	Indoor installation
Connections - terminals	ClampTite terminal
Mounting mode	Upright/horizontal
Diameter	75 mm
Height	233 mm
Net weight	1.2 kg

Environment

Standards	IEC 60831-2 IEC 60831-1
IP degree of protection	IP20
Operating altitude	2000 m
Temperature class	D
Ambient air temperature for operation	-25...55 °C
Relative humidity	95 %

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.500 cm
Package 1 Width	12.500 cm
Package 1 Length	28.500 cm
Package 1 Weight	1.319 kg
Unit Type of Package 2	S03
Number of Units in Package 2	6
Package 2 Height	30.000 cm
Package 2 Width	30.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	8.714 kg

Contractual warranty

Warranty (in months)	18
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Environmental footprint

Total lifecycle Carbon footprint 24

Environmental Disclosure [Product Environmental Profile](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard Yes

Packaging without single use plastic Yes

[EU RoHS Directive](#) Compliant

REACH Regulation [REACH Declaration](#)

Energy efficiency

Product contributes to saved and avoided emissions Yes

Use Longer

Lifetime extension

Repair No

Use Again

Repack and remanufacture

End of life manual availability [End of Life Information](#)

Take-back No

WEEE Label The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins