



Features

- IP66 rated protects against dust and powerful water jets, ideal for tough indoor and outdoor environments.
- Front mounted accessory frame provides universal compatibility with standard sized 2 gang accessories from other manufacturers
- Single latching clip provides quick and easy access to the accessory
- Translucent cover allows neon indicators to be seen when closed with locking points on cover allow use of a padlock to restrict access
- Grey impact resistant polycarbonate housing
- Fast fix screws allows accessory frame to be quickly installed and removed
- Back box mounting points separated from main wiring space to maintain IP rating
- Multiple drill out cable entry points on all sides and rear of back box

Technical Specification

- **Material** - Polycarbonate
- **IP Rating** - IP66
- **Overall Outer Dimensions (W x H x D)** - 188 x 170 x 90mm

IP66 2g Enclosure

Description

Weathersafe has been designed to withstand the toughest outdoor and demanding environments, combining reliability and long-lasting performance with a sleek black finish. Rated IP66 and manufactured from impact-resistant polycarbonate ensures the product endures harsh conditions, making it an ideal solution for gardens, patios, and workshops.

Front mounted accessory frame provides universal compatibility with standard sized 2 gang accessories from other manufacturers. Allows easy access with the single latching clip to open the hinged cover whilst maintaining the IP66 rating when closed. Neon indicator can be seen through the translucent cover to show status without the need to open the cover. To restrict unauthorised access, the cover can be locked and secured with a padlock.

Installation is quick and effortless. Fast-fix captive screws allow the detachable back box to be removed with ease, while mounting points are separated from the main wiring space minimising the need for weatherproof sealant to reinstate IP66 rating.

Product Code

IP66 2g Enclosure

TW1201

Compliance

- BS EN 60670-1
- BS EN 60529

Guarantee

- 10-year guarantee