






LV HRC FUSE BASE, 660V TRIPLE-POLE,
250A, SIZE 1

Similar to image

Technical data:

Design type		-
Product component / Retracting-equipment		No
Type of fixing/fixation / Runner Mondays		No
Current / for AC / rated value	A	250
Rated breaking capacity / DC	kA	25
Rated breaking capacity / AC	kA	120
rated voltage Un / AC	V	690
rated voltage Un / DC	V	440
Number of poles		3
Flat connector / max. torque	N-m	38
Terminal strip / max. torque for mounting the LV HRC base	N-m	2.5

Certificates/approvals:

General Product Approval	Test Certificates	Shipping Approval	other
 ROSTEST  UL	Manufacturer	 GL	Manufacturer

Further information:

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/lowvoltage/maill>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/3NH4230/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)


http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NH4230

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

[Datanorm](#) [GAEB81](#) [GAEB83](#) [RTF](#) [TXT](#)



last change:

Jan 18, 2012