

840-AG11D-ESL

x OBSOLETE

DIPLOMATE

TE Internal #: 1-1437540-7

TE Internal Description: 840-AG11D-ESL=SOCKET ASSY

[View on TE.com >](#)



Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2021 (211) SVHC > Threshold: Pb (13% in Component Part) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Reflow solder capable to 245°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought



TE Part #1-1658621-0
50 NOVO MIL/CTR 15DP,LEAD FREE




TE Part #3-87977-5
20 MODIV HSG COMP DR .100 POL




TE Part #8-52936-1
TERMINAL,PIDG SPR SPD 16-14 8



TE Part #200389-2
GUIDE PIN KIT



TE Part #5-1879665-0
H8 40K2 0.1% 15PPM



TE Part #281783-8
PLUG HE14 IDC 180 8 P AWG 26-24



TE Part #925486-1
MOD. IV SNAP-IN HSG 96 POS.



TE Part #6-1393122-7
KHAU-17D12N-110=KH



TE Part #2-1571586-9
828-AG11D-LF=800 DIP,PCB,AU/SN

Documents

Product Drawings

840-AG11D-ESL=SOCKET ASSY

English

CAD Files

3D PDF

English

Customer View Model

ENG_CVM_1-1437540-7_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_1-1437540-7_A.3d_igs.zip

English

Customer View Model

ENG_CVM_1-1437540-7_A.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Datasheets & Catalog Pages



DIP Sockets Quick Reference Guide (EN)

English