


Datasheet

RS Pro Polyamide Terminal Blocks

Stock No: 813-3123

SPECIFICATIONS

INSERTS: BRASS
HOUSING: POLYAMIDE (PA66)
TEMPERATURE 105°C
SCREWS: GALVANISED STEEL
STANDARDS: CE (BS EN 60998)
COLOUR: NATURAL
FEATURES: SEMI-RIGID & LOW COST
 FLAME RETARDANT
 HIGH TEMPERATURE
 ALL SCREWS ARE CAPTIVE &
 RAISED FOR EASY WIRING



| RS Stock No. | CROSS SECTION | CURRENT RANGE | RATED VOLTAGE | DIMENSIONS (mm) | | | | | | | |
|--------------|--------------------|---------------|---------------|-----------------|------|-----|-----|------|----|------|------|
| | | | | L | W | φ1 | φ2 | D | d | H | h |
| 813-3120 | 4 mm ² | 3 - 24 A | 380 V | 93 | 16.8 | 2.8 | 2.3 | 7.8 | 6 | 13.6 | 7.6 |
| 813-3123 | 6 mm ² | 5 - 32 A | 380 V | 114 | 18.8 | 3.3 | 2.6 | 10 | 8 | 15 | 8.8 |
| 813-3127 | 10 mm ² | 10 - 57 A | 400 V | 125 | 20.7 | 4.3 | 2.8 | 11 | 9 | 16.2 | 9.6 |
| 813-3136 | 12 mm ² | 15 - 61 A | 400 V | 137 | 22.5 | 4.5 | 2.8 | 12 | 10 | 18.8 | 10.2 |
| 813-3139 | 16 mm ² | 30 - 76 A | 400 V | 165 | 25.5 | 5.5 | 3 | 14 | 11 | 19.8 | 11.2 |
| 867-0988 | 25 mm ² | 60 - 101 A | 400 V | 187 | 31.2 | 6.5 | 3.8 | 16.5 | 13 | 25.5 | 14.8 |

Cross-section rated for rigid wire and cables (if for flexible wire, it should be reduced one-step, i.e., 6mm² is 4mm²)

φ1 = wire entry hole diameter

φ2 = fixing hole diameter