

PRODUCT SHEET

10-...N


Open end wrenches in mm

Forged from chrome vanadium steel.

2 openings per spanner. Bright polished finish.

30° working arc. High torque.

Shaped for a comfortable grip.



Normes : DIN 3110, DIN 3113, DIN ISO 1711-1, DIN ISO 691, ISO 10102, ISO 1711-1, ISO 3318, ISO 691, NF ISO 10102, NF ISO 1711-1, NF ISO 3318, NF ISO 691

reference	A1 mm	A2 mm	d1 mm	d2 mm	e mm	L mm	Weight g
10-3,2X5N	3.2	5	10	13		90	10
10-4X5N	4	5	13	15		110	15
10-5X7N	5	7	13	15		110	18
10-5,5X7N	5.5	7		19		128	20
10-6X7N	6	7				124	22
10-6X8N	6	8				124	22
10-8X9N	8	9				144	30
10-8X10N	8	10		23		144	38
10-10X11N	10	11				159	46
10-10X12N	10	12				159	48
10-10X13N	10	13			5	172	58
10-11X13N	11	13			5	172	65
10-12X13N	12	13			5	172	67
10-12X14N	12	14			5	176	69
10-13X14N	13	14				176	79
10-13X15N	13	15				188	86

PRODUCT SHEET

10-13X17N	13	17		37	6	192	107
10-14X15N	14	15				188	87
10-14X16N	14	16				188	87
10-14X17N	14	17		37	6	192	93
10-16X17N	16	17		37		202	116
10-16X18N	16	18		39		202	119
10-17X19N	17	19	37			220	154
10-18X19N	18	19				220	149
10-20X21N	20	21		46		239	188
10-20X22N	20	22		46		239	188
10-21X23N	21	23				249	224
10-22X23N	22	23				249	224
10-22X24N	22	24				249	245
10-24X25N	24	25				261	294
10-24X26N	24	26				261	294
10-24X27N	24	27				261	294
10-24X30N	24	30				261	294
10-25X28N	25	28				280	356
10-26X27N	26	27				261	345
10-26X28N	26	28				280	356
10-27X29N	27	29				297	460
10-27X30N	27	30				297	460
10-27X32N	27	32				295	475
10-30X32N	30	32				300	475
10-32X35N	32	35				313	535
10-34X36N	34	36				329	590
10-36X41N	36	41				358	984
10-38X42N	38	42				358	984