

DCLE14201RB-XJ

USB Cross Line Red Beam Laser



5035048810682



Product Description :

The DEWALT DCLE14201RB-XJ USB Cross Line Red Beam Laser is a lightweight, 30m ranged cross line laser that incorporates POWERSTACK™ Technology.

The integrated USB battery, charged by USB-C Cable, utilises POWERSTACK™ battery technology to last a minimum of 10 hours when fully charged. Even though the laser can be used when plugged in, it will achieve 80% charge in as little as 30 minutes.

The DCLE14201 delivers a red cross line beam that has a working range of 30m or 50m when used with a detector. With an enhanced accuracy of +/- 3mm @ 10m, the laser provides professional accuracy and ensures precision when on the job.

As well as Manual Slope, Self Level and Pendulum Lock, the USB Cross Line Red Beam Laser includes a beam brightness adjustment control to suit general lighting conditions on site, while the pivotable bracket with magnets that offer a flush attachment to either metal tracking or to steel works.

With IP65 rating to protect it against the elements, the DCLE14201 can also be attached to a tripod thanks to the 1/4" or 5/8" tripod thread on the bracket.

Product Features and Benefits :

- Recharges in 30min using a 45W USB-PD Charger(Not Included): Minimal Downtime, Ability to Charge While Using Continuously. If Charging is Required on Site Can be Done In Conjunction with Working Allowing for no Downtime. Quick Charging Increases Productivity, Ensures One Charge will Last a Whole Job.
- Pivotable Bracket with Magnets: Flush Attachment to Metal and Steelwork, can be used and Stabilised in Many Working Environments INCLUDES
- Beam Brightness Adjustment: 3 Settings to Adjust to Light Levels on Jobsite Ensuring Visibility Regardless of Environment
- Compact Size & Storage Case : Easily Stored in Toolbox & Tool Bags
- 3mm Accuracy @ 10m: Professional Precision and Accuracy
- Fine Adjustment Knob: For Precise Rotational Positioning of the Laser Line Ensuring Accuracy. Saving Time Whilst Increasing Productivity
- Red Beam Diode: Upto 30m Visibility & 50m with Detector (Sold Separately) Ensures better Visibility on the Jobsite
- 11 Hour RunTime: Runs for a Full Day on The Jobsite Without Downtime
- IP65: Water/ Debris Resistance for Dependable Jobsite Use
- Manual Slope Function @ 4° : Allowing the Application for Staircase, Ramps etc

Product Warranty :

1 Year Limited Warranty, 3 Year Limited Warranty When Registered

