

Dust Extractor XGT®

VC005GL

40Vmax • 230 mbar • 8 L • L

XGT® Battery powered dust extractor for cleaning.

A versatile dust extractor that runs on with XGT® battery. The batteries can be connected in parallel. It Matches filter class: L HEPA . Tank capacity is 8 L which enables continuous cleaning work.



Technical specifications

Vacuum hose length	1,7 m
Vacuum hose diameter	32 mm
Voltage XGT	✓
Nominal Battery Voltage	40 V
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Air volume	2,8 m³/min
Max. sealed suction	230 mbar
Suction power	265 W
Continuous Use XGT® 40V Max / 5.0 Ah X2	28 - 220 min
Tank Capacity for Dust	8 L
Sound Pressure Level (L _{pA})	≤ 70 dB(A)
Product net weight	7,2 kg
Noise Uncertainty (K Factor)	2,5 dB(A)
Tool weight with battery	7,9 - 11,0 kg
Product Dimensions (L x W x H):	366 x 334 x 397 mm

User benefits

- Quiet operation for operator comfort
- Flat top design for space saving in storage
- Carry handle for easy transportation
- Approved for Dust Class L in accordance with the EU standard
- Battery protection system automatically shuts off power when the battery level is low

Link to product - www.makitauk.com



Related products

Other

User manual

Parts drawing