

HUBER+SUHNER® DATA SHEET

Within Series Adaptor: 31_716-50-0-2/133_W

Rev.: D 

Description

Adaptor jack/jack
7/16 jack (female) / 7/16 jack (female)

Low intermodulation adaptors
For Test & Measurement applications

Interface standard
Series 7/16 - IEC 61169-4_CECC 22190_DIN 47223_VG 95250



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	7.5 GHz
PIM, 3 rd order intermodulation distortion (IMD) max.	Static -165 dBc at 2x 43 dBm / 20 W carrier

Mechanical Data

Number of matings	500
Weight	0.1399 kg

Environmental Data

Operating Temperature	-65 °C to 165 °C
2002/95/EC (RoHS)	compliant

Material Data

Piece Parts

Interface - 7/16 jack (female)

	Material
Centre contact	Copper Beryllium Alloy
Outer contact	Brass
Body	Brass
Insulator	PFA / PTFE

Surface Plating

SUCOPRO Plating
SUCOPLATE (R) Plating
SUCOPLATE (R) Plating

Interface - 7/16 jack (female)

Centre contact	Copper Beryllium Alloy
Outer contact	Brass
Body	Brass
Insulator	PFA / PTFE

SUCOPRO Plating
SUCOPLATE (R) Plating
SUCOPLATE (R) Plating

Related Documents

Outline drawing	DOU-00013798
-----------------	--------------

Ordering Information

Single package	31_716-50-0-2/133_WE
----------------	----------------------

HUBER+SUHNER is certified according to ISO 9001 and ISO 14001

WAIVER!

It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical contained specifications and/or the fitness for any particular purpose. The facts and figures herein are carefully compiled to the best of our knowledge, but they are intended for general informational purposes only.



HUBER+SUHNER AG
RF Protection
9100 Herisau, Switzerland
Phone +41 (0)71 353 41 11
Fax +41 (0)71 353 47 51
www.hubersuhner.com

HUBER+SUHNER – Excellence in Connectivity Solutions