

Commercial status: Commercialised



Main

Range	Acti9
Product or component type	Add-on residual current devices
Device short name	Vigi iTG40
Range compatibility	Acti9 iDT40
Poles description	3P + N
Neutral position	Left
[In] rated current	25 A
Network type	AC
Earth-leakage sensitivity	300 mA
Earth-leakage protection time delay	Instantaneous
Earth-leakage protection class	Type AC
Product certifications	CE
Quality labels	NF

Complementary

Device location in system	Group incomer
Network frequency	50 Hz
[Ue] rated operational voltage	400 V AC 50 Hz
Residual current tripping technology	Voltage independent
[Ui] rated insulation voltage	440 V AC 50/60 Hz conforming to EN/IEC 61009-2-1
[Uimp] rated impulse withstand voltage	4 kV conforming to EN/IEC 61009-2-1
Local signalling	Fault indication
Mounting mode	Clip-on
Mounting support	DIN rail
Electrical connection to mcb	By screws
9 mm pitches	6
Height	91 mm
Width	108 mm
Depth	74 mm
Colour	White
Mechanical durability	20000 cycles
Electrical durability	10000 cycles
Connections - terminals	Tunnel type terminal top1...16 mm ² rigid Tunnel type terminal top1...10 mm ² flexible
Wire stripping length	14 mm for top connection
Tightening torque	2 N.m top

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environment

Standards	EN/IEC 61009-2-1
IP degree of protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
Pollution degree	3 conforming to EN/IEC 61009-2-1
Relative humidity	95 % at 55 °C
Operating altitude	2000 m
Ambient air temperature for operation	-5...60 °C
Ambient air temperature for storage	-40...85 °C

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Under investigation
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 mois
----------	---------