




Brand of NTN corporation

Technical data



6024EE

Single row deep groove ball bearings



Deep groove ball bearing, radial contact, pressed steel cage, contact seals on both sides

VISUAL (S)



NTN Europe

1 rue des Usines · BP 2017 · 74010 Annecy Cedex · France · Tel. +33 (0)4 50 65 30 00
S.A. au capital de 322 639 919 € · RCS ANNECY B 325 821 072 · Id. Fiscale : FR 48 325 821 072
SIRET 325 821 072 00015 · Code APE 2815 Z · Code NACE 28.15

PRODUCT DEFINITION

Brand	SNR
d - Internal diameter	120 mm
D - External diameter	180 mm
B - Bearing/Inner ring width	28 mm
d1 - External diameter inner ring	135,3 mm
D1 - Inner diameter outer ring	165,2 mm
rs - Min fillet radius	2 mm
Radial clearance class	CN
Mass	2,04 kg

PRODUCT PERFORMANCE

C - Dynamic load	92900000 mN
C0 - Static load	80000000 mN
Cu - Fatigue limit load	2950000 mN
f0 - Coefficient	15.7
N lim - Mechanical Limit Speed	12600 °/s
Tmin - Min operating temperature	243,15 °K
Tmax - Max operating temperature	393,15 °K

BEARING FREQUENCIES

BPFO - Over rolling frequency on outer ring (60 rpm)	6.111 Hz
BPFI - Over rolling frequency on inner (60 rpm)	7.889 Hz
BSF - Over rolling frequency on rolling element (60 rpm)	7.747 Hz
BRF - Rotational frequency - rolling element (60 rpm)	3.874 Hz
FTF - Rotational frequency - cage (60 rpm)	0.436 Hz



ABUTMENT

da min - Min shoulder diameter IR	129 mm
da max - Max shoulder diameter IR	135,3 mm
Da max - Max shoulder diameter OR	171 mm
ra max - Max shaft & housing fillet radius	2 mm

INDUSTRY CALCUL FACTORS

Equivalent dynamic radial load

$$P = X.F_r + Y.F_a$$

$\frac{f_0 F_a}{C_0}$	e	Fa / Fr ≤ e		Fa / Fr > e	
		X	Y	X	Y
0.172	0.19	1	0	0.56	2.3
0.345	0.22				1.99
0.689	0.26				1.71
1.03	0.28				1.55
1.38	0.3				1.45
2.07	0.34				1.31
3.45	0.38				1.15
5.17	0.42				1.04
6.89	0.44				1

Equivalent static radial load

$$P_0 = X_0.F_r + Y_0.F_a$$

X_0	Y_0
0.6	0.5

For single or DT bearing arrangement :

If $P_0 < F_r$, then use $P_0 = F_r$

