

# SACC-DSI-M8FS-5CON-M10-L180 DN - Device connector rear mounting



1424241

<https://www.phoenixcontact.com/gb/products/1424241>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Device connector rear mounting, 5-position, Socket, straight, M8, coding: B, Rear mounting, M10, Wave soldering

## Your advantages

- Easy PCB assembly: one-piece connectors for wave soldering
- For high transmission reliability: optional shield connection to the housing and latching on the PCB

## Commercial data

Item number	1424241
Packing unit	20 pc
Minimum order quantity	20 pc
Sales key	ABQJBB
Product key	ABQJBB
Catalog page	Page 229 (C-2-2013)
GTIN	4046356712538
Weight per piece (including packing)	6.79 g
Weight per piece (excluding packing)	5.1 g
Customs tariff number	85366990
Country of origin	DE



# SACC-DSI-M8FS-5CON-M10-L180 DN - Device connector rear mounting



1424241

<https://www.phoenixcontact.com/gb/products/1424241>

## Technical data

### Mounting

Mounting type	Rear mounting M10 With flat nut
Assembly note	With flat nut

### Product properties

Product type	Circular connectors (device side)
Number of positions	5
Shielded	yes
Coding	B
Thread type	M8

### Insulation characteristics

Overvoltage category	II
Degree of pollution	3

### Material specifications

Flammability rating according to UL 94	HB
Contact material	Cu alloy
Contact surface material	Au
Contact carrier material	PA 6.6
Material for screw connection	Zinc die-cast, nickel-plated

### Electrical properties

Contact resistance	$\leq 3 \text{ m}\Omega$
Insulation resistance	$\geq 100 \text{ M}\Omega$
Nominal voltage $U_N$	30 V AC
	30 V DC
Nominal current $I_N$	3 A

### Connection data

#### Conductor connection

Connection method	Wave soldering
Contact connection type	Socket

### Connector

#### Connection 1

Head design	Socket
Head cable outlet	straight
Head thread type	M8
Coding	B



# SACC-DSI-M8FS-5CON-M10-L180 DN - Device connector rear mounting



1424241

<https://www.phoenixcontact.com/gb/products/1424241>

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP67
	IP67
Ambient temperature (operation)	-25 °C ... 85 °C
	-25 °C ... 85 °C

## Standards and regulations

Standard designation	M8 circular connector
Standards/specifications	according to IEC 61076-2-104




# SACC-DSI-M8FS-5CON-M10-L180 DN - Device connector rear mounting

1424241

<https://www.phoenixcontact.com/gb/products/1424241>

## Drawings

Schematic diagram




connector pin assignment of M8 socket, 4-pos., view of pin side




1424241  
<https://www.phoenixcontact.com/gb/products/1424241>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1424241>

<div> <b>cUL Recognized</b> Approval ID: E221474-20070307</div>				
	Nominal voltage U <sub>N</sub>	Nominal current I <sub>N</sub>	Cross section AWG	Cross section mm <sup>2</sup>
	30 V	4 A	24	-

<div> <b>UL Recognized</b> Approval ID: E221474-20070307</div>				
	Nominal voltage U <sub>N</sub>	Nominal current I <sub>N</sub>	Cross section AWG	Cross section mm <sup>2</sup>
	30 V	4 A	24	-



# SACC-DSI-M8FS-5CON-M10-L180 DN - Device connector rear mounting



1424241  
<https://www.phoenixcontact.com/gb/products/1424241>

## Classifications

### ECLASS

ECLASS-13.0	27440110
-------------	----------

### ETIM

ETIM 9.0	EC003569
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------



# SACC-DSI-M8FS-5CON-M10-L180 DN - Device connector rear mounting



1424241

<https://www.phoenixcontact.com/gb/products/1424241>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	36920a30-dc71-4ad5-9a08-386308640d1c

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)