

# Product data sheet

Specifications



APC Smart-UPS On-Line, 2200VA,  
Lithium-ion, Rackmount 4U, 230V,  
6x C13+2x C19 IEC outlets,  
SmartSlot, Extended long runtime,  
Rail kit included

SRTL2200RM4UXLI

ⓘ Discontinued

## Overview

|              |                                                                             |
|--------------|-----------------------------------------------------------------------------|
| Presentation | High density, double-conversion on-line power protection with long runtime. |
| Lead time    | Usually in Stock                                                            |

## Main

|                           |                                    |
|---------------------------|------------------------------------|
| Main Input Voltage        | 230 V                              |
| Product or Component Type | Uninterruptible power supply (UPS) |
| Other Input Voltage       | 220 V                              |
| Main Output Voltage       | 230 V                              |
| Other Output Voltage      | 220 V                              |
| Kw Rating                 | 1980 W                             |
| rated power in VA         | 2200 VA                            |
| Input Connection Type     | IEC 60320 C20                      |
| output connection type    | 6 IEC 60320 C13                    |
| Number of rack unit       | 4U                                 |
| Cable length              | 6 ft (1.8 m)                       |
| Number of cables          | 1                                  |
| Range of Product          | Smart-UPS On-Line                  |

## Batteries & Runtime

|                              |                                       |
|------------------------------|---------------------------------------|
| Run Time                     | <a href="#">View Runtime Graph</a>    |
| Efficiency                   | <a href="#">View Efficiency Graph</a> |
| Battery Type                 | Li-Ion (Lithium Ion)                  |
| Battery Voltage              | 48V                                   |
| Extendable Run Time          | 1                                     |
| Included Battery Modules     | 0                                     |
| Battery Slots Empty          | 0                                     |
| Battery life                 | 5...10 year(s)                        |
| Battery Charge Power (Watts) | 158 W rated                           |

## General

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

|                                     |                          |
|-------------------------------------|--------------------------|
| Number of power module filled slots | 0                        |
| Number of power module free slots   | 0                        |
| product web sub-family              | Lithium Ion              |
| Redundant                           | No                       |
| Topology                            | Double Conversion Online |

## Physical

|                     |                               |
|---------------------|-------------------------------|
| color               | Black with silver front bezel |
| Height              | 6.73 in (17.1 cm)             |
| Width               | 17.01 in (43.2 cm)            |
| Depth               | 25.16 in (63.9 cm)            |
| Net Weight          | 95.2 lb(US) (43.2 kg)         |
| Mounting preference | No preference                 |
| Mounting Mode       | Rack-mounted with kit         |
| Two post mountable  | 0                             |
| USB compatible      | Yes                           |
| Mounting position   | Horizontal<br>Vertical        |

## Input

|                         |                         |
|-------------------------|-------------------------|
| Efficiency at full load | 160...275 V             |
| Input Frequency         | 40 - 70 Hz auto-sensing |

## Output

|                                  |                                 |
|----------------------------------|---------------------------------|
| Bypass type                      | Built-in Bypass                 |
| Crest factor                     | 3 : 1                           |
| Harmonic distortion              | Less than 2%                    |
| Maximum configurable power in VA | 2200 VA                         |
| Max Configurable Power (Watts)   | 1980 W                          |
| Wave type                        | Sine wave                       |
| Output Frequency (sync to mains) | 50/60 Hz +/- 3 Hz sync to mains |

## Conformance

|                        |               |
|------------------------|---------------|
| Product Certifications | CE<br>UK PSTI |
| Marking                | CE Mark       |

## Environmental

|                                       |                         |
|---------------------------------------|-------------------------|
| Acoustic level                        | 50 dBA                  |
| Online Thermal Dissipation            | 317 Btu/h               |
| Operating altitude                    | 0...10000 ft            |
| Ambient air temperature for operation | 32...104 °F (0...40 °C) |

|                                     |                                                  |
|-------------------------------------|--------------------------------------------------|
| Ambient Air Temperature for Storage | -4...122 °F (-20...50 °C)                        |
| Storage altitude                    | 0...50000 ft (0.0000000000...15240.0000000000 m) |
| IP degree of protection             | IP20                                             |
| Relative Humidity                   | 0...95 % non-condensing                          |
| Storage Relative Humidity           | 0...95 % non-condensing                          |

## Communications & Management

|                           |                                                      |
|---------------------------|------------------------------------------------------|
| Emergency Power Off (EPO) | Yes                                                  |
| Free slots                | 1                                                    |
| Alarm                     | Audible and visible alarms : prioritized by severity |

## Surge Protection and Filtering

|                     |       |
|---------------------|-------|
| Surge energy rating | 432 J |
|---------------------|-------|

## Ordering and shipping details

|      |              |
|------|--------------|
| GTIN | 731304508977 |
|------|--------------|

## Packing Units

|                              |                        |
|------------------------------|------------------------|
| Unit Type of Package 1       | PCE                    |
| Number of Units in Package 1 | 1                      |
| Package 1 Height             | 9.65 in (24.5 cm)      |
| Package 1 Width              | 23.62 in (60 cm)       |
| Package 1 Length             | 31.89 in (81 cm)       |
| Package 1 Weight             | 124.6 lb(US) (56.5 kg) |

## Contractual warranty

|          |                          |
|----------|--------------------------|
| Warranty | 5 year repair or replace |
|----------|--------------------------|

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

Environmental footprint

Environmental Disclosure

[Product Environmental Profile](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard

Yes

Packaging without single use plastic

No

[EU RoHS Directive](#)

Compliant with Exemptions

REACH Regulation

[REACH Declaration](#)

Use Again

Repack and remanufacture

Circularity Profile

[End of Life Information](#)

Removable battery

User replaceable

Take-back

No