



### Main

Range of product	EZD
Product or component type	Circuit breaker
Device short name	EZD160E
Circuit breaker application	Distribution
Poles description	4P
Protected poles description	3d

### Complementary

Earth-leakage protection	Without
[In] rated current	125 A 40 °C
Breaking capacity code	E
Network type	AC
Network frequency	50/60 Hz
Control type	Toggle
Mounting mode	Fixed
Mounting support	Backplate
Upside connection	Front
Downside connection	Front
[Ui] rated insulation voltage	690 V EN/IEC 60947-2
[Uimp] rated impulse withstand voltage	6 kV EN/IEC 60947-2
[Ue] rated operational voltage	500 V EN/IEC 60947-2 AC 50/60 Hz
Breaking capacity	50 kA Icu EN/IEC 60947-2 220/230 V AC 50/60 Hz 25 kA Icu EN/IEC 60947-2 380/400 V AC 50/60 Hz 25 kA Icu EN/IEC 60947-2 415 V AC 50/60 Hz 20 kA Icu EN/IEC 60947-2 440 V AC 50/60 Hz 8 kA Icu EN/IEC 60947-2 500 V AC 50/60 Hz
Utilisation category	Category A
[Ics] rated service breaking capacity	25 kA EN/IEC 60947-2 220/230 V AC 50/60 Hz 13 kA EN/IEC 60947-2 380/400 V AC 50/60 Hz 13 kA EN/IEC 60947-2 415 V AC 50/60 Hz 10 kA EN/IEC 60947-2 440 V AC 50/60 Hz 4 kA EN/IEC 60947-2 500 V AC 50/60 Hz
Mechanical durability	10000 cycles
Electrical durability	5000 cycles EN/IEC 60947-2 440 V In
Connection pitch	35 mm
Trip unit name	TM-D
Trip unit technology	Thermal-magnetic
Trip unit rating	125 A 40 °C
Protection type	Overload protection (thermal) Short-circuit protection (magnetic)
Long time pick-up adjustment type I <sub>r</sub>	Fixed
Long time pick-up adjustment range	1 I <sub>n</sub>
Instantaneous pick-up adjustment type I <sub>i</sub>	Fixed
Integral instant protection	1250 kA
Height	165 mm

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Width	140 mm
Depth	68 mm
Product weight	2.1 kg
Compatibility code	EZD160

## Environment

Standards	EN 60947-2 IEC 60947-2
Pollution degree	3 IEC 60947-1
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-50...85 °C

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0726 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Available