

Eaton 231835

Catalog Number: 231835

Eaton Moeller® series DILER Contactor relay, 48 V 50 Hz, N/O = Normally open: 4 N/O, Spring-loaded terminals, AC operation

General specifications



Product Name	Catalog Number
Eaton Moeller® series DILER Control relay	231835
	EAN
	4015082318352
Product Length/Depth	Product Height
52 mm	58 mm
Product Width	Product Weight
45 mm	0.17 kg

Certifications

- CSA
- CE
- CSA Class No.: 3211-03
- UL Category Control No.: NKCR
- CSA File No.: 012528
- UL
- UL 508
- CSA-C22.2 No. 14-05
- EN 60947-5-1
- UL File No.: E29184
- IEC/EN 60947
- IEC/EN 60947-4-1
- VDE 0660

Features & Functions

Features

Positive operating contacts to EN 60947-5-1 appendix L, including auxiliary contact module

Fitted with:

Interlocked opposing contacts

General

Application

Contactor relays

Lifespan, mechanical

10,000,000 Operations (AC operated)

Mounting method

DIN-rail/screw

Mounting position

As required (except vertical with terminals A1/A2 at the bottom)

Operating frequency

9000 Operations/h

Overvoltage category

III

Pollution degree

3

Product category

DILER Mini-contactors

Protection

Finger and back-of-hand proof, Protection against direct contact when actuated from front (EN 50274)

Rated impulse withstand voltage (Uimp)

6000 V AC

Shock resistance

10 g, N/O auxiliary contact, Basic unit with auxiliary contact module, Mechanical, according to IEC/EN 60068-2-27, Half-sinusoidal shock 10 ms

8 g, N/C auxiliary contact, Basic unit with auxiliary contact module, Mechanical, according to IEC/EN 60068-2-27, Half-sinusoidal shock 10 ms

Voltage type

AC

Climatic environmental conditions

Ambient operating temperature - min

-25 °C

Ambient operating temperature - max

50 °C

Terminal capacities

Terminal capacity (flexible with ferrule)

1 x (1 - 2.5) mm²

2 x (1 - 2.5) mm²

Terminal capacity (solid/stranded AWG)

Ambient operating temperature (enclosed) - min
25 °C

Ambient operating temperature (enclosed) - max
40 °C

Climatic proofing
Damp heat, constant, to IEC 60068-2-78
Damp heat, cyclic, to IEC 60068-2-30

1 x (16 - 14)
2 x (16 - 14)

Stripping length (main cable)
10 mm

Screwdriver size
0.6 x 3.5 mm, Spring-loaded terminals

Electrical rating

Rated operational voltage (Ue) at AC - max
600 V

Rated insulation voltage (Ui)
690 V

Rated operational current (Ie)
1.5 A at 110 V, DC L/R ≤ 15 ms (with 3 contacts in series)
2.5 A at 24 V, DC L/R ≤ 15 ms (with 1 contact in series)
2.5 A at 60 V, DC L/R ≤ 15 ms (with 2 contacts in series)
0.5 A at 220 V, DC L/R ≤ 15 ms (with 3 contacts in series)
10 A

Rated operational current (Ie) at AC-15, 220 V, 230 V, 240 V
6 A

Rated operational current (Ie) at AC-15, 380 V, 400 V, 415 V
3 A

Rated operational current (Ie) at AC-15, 500 V
1.5 A

Safe isolation
300 V AC, Between auxiliary contacts, According to EN 61140
300 V AC, Between coil and auxiliary contacts, According to EN 61140

Short-circuit rating

Short-circuit protection rating
10 A fast, 500V, Maximum fuse, Short-circuit rating without welding, Contacts

Short-circuit protection rating without welding
6 A gG/gL, 500 V, Max. Fuse, Contacts

Switching capacity

Switching capacity (auxiliary contacts, general use)
10 A, 600 V AC, (UL/CSA)
0.5 A, 250 V DC, (UL/CSA)

Switching capacity (auxiliary contacts, pilot duty)
A600, AC operated (UL/CSA)

Magnet system

Duty factor

100 %

Pick-up voltage

0.8 - 1.1 V AC x U_c (voltage tolerance - single-voltage coil 50 Hz and dual-voltage coil 50 Hz, 60 Hz)

0.85 - 1.1 V AC x U_c (voltage tolerance - dual frequency coil 50/60 Hz)

Power consumption, pick-up, 50 Hz

25 VA, AC, Single-frequency coil 50 Hz and Dual-frequency coil 50/60 Hz

Power consumption, pick-up, 60 Hz

25 VA, AC, Single-frequency coil 50 Hz and Dual-frequency coil 50/60 Hz

Power consumption, sealing, 50 Hz

4.6 VA, AC, Single-frequency coil 50 Hz and Dual-frequency coil 50/60 Hz

1.3 W, AC, Single-frequency coil 50 Hz and Dual-frequency coil 50/60 Hz

Power consumption, sealing, 60 Hz

1.3 W, AC, Single-frequency coil 50 Hz and Dual-frequency coil 50/60 Hz

Rated control supply voltage (U_s) at AC, 50 Hz - min

48 V

Rated control supply voltage (U_s) at AC, 50 Hz - max

48 V

Rated control supply voltage (U_s) at AC, 60 Hz - min

0 V

Rated control supply voltage (U_s) at AC, 60 Hz - max

0 V

Rated control supply voltage (U_s) at DC - min

0 V

Rated control supply voltage (U_s) at DC - max

0 V

Switching time (AC operated, make contacts, closing delay) - min

14 ms

Switching time (AC operated, make contacts, closing delay) - max

21 ms

Switching time (AC operated, make contacts, opening delay) - min

8 ms

Switching time (AC operated, make contacts, opening delay) - max

18 ms

Switching time (AC operated, N/O, with auxiliary contact module, closing delay)

45 ms

Contacts

Code number

40E

Control circuit reliability

$< 2 \lambda, < 1$ failure at 100,000,000 Operations (at $U_e = 24$ V DC, $U_{min} = 17$ V, $I_{min} = 5.4$ mA)

Number of auxiliary contacts (change-over contacts)

0

Number of auxiliary contacts (normally closed contacts)

0

Number of auxiliary contacts (normally open contacts)

4

Design verification

Equipment heat dissipation, current-dependent P_{vid}

0 W

Heat dissipation capacity P_{diss}

0 W

Heat dissipation per pole, current-dependent P_{vid}

0.4 W

Rated operational current for specified heat dissipation (I_n)

6 A

Static heat dissipation, non-current-dependent P_{vs}

1.8 W

10.2.2 Corrosion resistance

Meets the product standard's requirements.

10.2.3.1 Verification of thermal stability of enclosures

Meets the product standard's requirements.

10.2.3.2 Verification of resistance of insulating materials to normal heat

Meets the product standard's requirements.

10.2.3.3 Resist. of insul. mat. to abnormal heat/fire by internal elect. effects

Meets the product standard's requirements.

10.2.4 Resistance to ultra-violet (UV) radiation

Meets the product standard's requirements.

Resources

Catalogs

[Product Range Catalog Switching and protecting motors](#)

[Switching and protecting motors - catalog](#)

[eaton-product-overview-for-machinery-catalogue-ca08103003zen-en-us.pdf](#)

Characteristic curve

[eaton-contactors-diler-relay-characteristic-curve.eps](#)

Declarations of conformity

[DA-DC-00004763.pdf](#)

[DA-DC-00004748.pdf](#)

Drawings

[eaton-contactors-diler-dimensions-002.eps](#)

[eaton-contactors-diler-dimensions.eps](#)

[eaton-tripping-devices-mounting-diler-contactor-relay-symbol.eps](#)

eCAD model

[ETN.231835.edz](#)

Installation instructions

[IL03407009Z](#)

mCAD model

[DA-CS-dil_em_c](#)

[DA-CD-dil_em_c](#)

System overview

10.2.5 Lifting

Does not apply, since the entire switchgear needs to be evaluated.

Wiring diagrams

[eaton-contactors-contact-diler-relay-wiring-diagram.eps](#)

10.2.6 Mechanical impact

Does not apply, since the entire switchgear needs to be evaluated.

10.2.7 Inscriptions

Meets the product standard's requirements.

10.3 Degree of protection of assemblies

Does not apply, since the entire switchgear needs to be evaluated.

10.4 Clearances and creepage distances

Meets the product standard's requirements.

10.5 Protection against electric shock

Does not apply, since the entire switchgear needs to be evaluated.

10.6 Incorporation of switching devices and components

Does not apply, since the entire switchgear needs to be evaluated.

10.7 Internal electrical circuits and connections

Is the panel builder's responsibility.

10.8 Connections for external conductors

Is the panel builder's responsibility.

10.9.2 Power-frequency electric strength

Is the panel builder's responsibility.

10.9.3 Impulse withstand voltage

Is the panel builder's responsibility.

10.9.4 Testing of enclosures made of insulating material

Is the panel builder's responsibility.

10.10 Temperature rise

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

10.11 Short-circuit rating

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.12 Electromagnetic compatibility

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.13 Mechanical function

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.
All other trademarks are property of their respective owners.



Eaton.com/socialmedia