



Relays & Contactors > Relay Accessories



Relay Socket Type: **Printed Circuit Board**

Body Material: **Polyester**

Product Mount Type: **Board Mount**

Pole Configuration: **2**

Relay Accessory Type: **Socket**

Features

Product Type Features

Relay Accessory Type	Socket
----------------------	--------

Configuration Features

Relay Options	Grounding Provision
---------------	---------------------

Body Features

Body Material	Polyester
---------------	-----------

Contact Features

Contact Material	Spring Brass
Contact Plating Material	Tin
Terminal Style	PC Stag
Relay Socket Type	Printed Circuit Board
Pole Configuration	2

Termination Features

Number of Pins	10
Termination Post & Tail Length	4.57 mm[.18 in]

Mechanical Attachment

Product Mounting Feature Type	Side lock
Product Mount Type	Board Mount

Other



Relays Comment	Strip Grounding
----------------	-----------------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 6-1393769-9
R10S-E1P2-J1.0K=R10



TE Part # 7-2027513-6
R10-E1P2-V2.5K=RELAY,2C,
BIFURCATED,DRY,S



TE Part # 1-1393766-1
R10-E1X2-24V=R10



TE Part # 1393766-6
R10-E1X2-V2.5K=R10



TE Part # 1393766-3
R10-E1X2-S800=R10



TE Part # 3-1393766-9
R10-E1Y2-V15.0K=R10



TE Part # 3-1393159-5
20C249=SPRING,HOLD-DOWN,R10,.0



TE Part # 5-1393769-5
R10-E1Z2-J1.0K=R10



TE Part # 3-1393766-6
R10-E1Y2-S200=R10



TE Part # 7-1393769-6
R10S-E1Y2-J500=R10



TE Part # 4-1393159-0
20C259=SPRING,HOLD-DOWN,R10,.0



TE Part # 4-1393766-4
R10-E1Y2-V700=R10



TE Part # 7-1393766-1
R10-E1Z2-V15.0K=R10



TE Part # 7-1393766-3
R10-E1Z2-V2.5K=R10



TE Part # 9-1393765-9
R10-E1X2-J5.0K=R10



TE Part # 7-1393766-2
R10-E1Z2-V185=R10



TE Part # 6-1393765-6
R10-E1P2-J2.5K=R10



TE Part # 6-1393765-9
R10-E1P2-V700=R10



TE Part # 6-1393765-8
R10-E1P2-V185=R10




TE Part # 7-1393769-5
R10S-E1Y2-J5.0K=R10


Also in the Series | **Potter & Brumfield R10**




AC Relays(9)



DC Relays(96)



Electromechanical Relays(105)



General Purpose Signal Relays(105)



PCB Headers & Receptacles(1)



Plug-In Relays(77)



Relay Accessories(27)

Customers Also Bought



TE Part #2-1445050-2
MICRO MNL HDR ASSY S/ROW LF



TE Part #354064-E
SMCB 32 F AB VV 7-03 CL * H007 137 E002




TE Part #6-1393765-9
R10-E1P2-V700=R10




TE Part #5145154-8
STANDARD EDGE .050 SERIES 60 DUAL ASSY




TE Part #5749268-1
Mini DIN, 8 pos, R/A, Shield



TE Part #5-103166-1
06 MODII HDR DRRA SHRD LF




TE Part #284314-E
STVE 160 F ABCDE VVVV 7-00 TL 4,0 * 247



TE Part #5-147278-4
05 MTE HDR SRRA SFMNT .100CL



TE Part #HD36-24-23PN-059
PLG,23P,AL,N, CBL CLMP BT, DRAIN, 16,P,MC



TE Part #106740-4
160P.IEC-C.M.CONN.

Documents

- CAD Files
- Customer View Model
- ENG_CVM_CVM_1-1393143-1_B.2d_dxf.zip
- English
- 3D PDF
- 3D
- Customer View Model
- ENG_CVM_CVM_1-1393143-1_B.3d_igs.zip



English

Customer View Model

ENG_CVM_CVM_1-1393143-1_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

R10 Sockets & Accessories

English

Product Specifications

Definitions General Purpose Relays

English

Agency Approvals

UL

English