



Connectors > Lighting Connectors > Plug & Socket Lighting Connectors



Connector System: **Cable-to-Cable**

Number of Positions: **2**

Sealable: **No**

Connector & Contact Terminates To: **Wire & Cable**

Lighting Connector Style: **Plug**

Features

Product Type Features

Connector System	Cable-to-Cable
Sealable	No
Connector & Contact Terminates To	Wire & Cable
Lighting Connector Style	Plug
Connector Product Type	Housing

Configuration Features

Keying Arrangement	HV-3
Number of Positions	2

Electrical Characteristics

Operating Voltage	42 VDC
-------------------	--------

Body Features

Primary Product Color	White
-----------------------	-------

Contact Features

Contact Type	Socket
--------------	--------



Mechanical Attachment

Connector Mounting Type	Cable Mount (Free-Hanging)
-------------------------	----------------------------

Operation/Application

Circuit Application	Power
---------------------	-------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 293388-3  
NECTOR S PLUG HV-4 WHITE



TE Part # 293390-1  
MICRO QUADLOK SYSTEM SOCKET CONTACT



Also in the Series

NECTOR S

Insertion & Extraction Tools(3)	Plug & Socket Lighting Connector Accessories(38)	Plug & Socket Lighting Connectors(30)	Power Terminals(4)

Customers Also Bought

TE Part #81665-5 ECONOSEAL, FLANGE GASKET	TE Part #929963-1 STIFTKONTAKT 2,5MMD	TE Part #925856-2 WIRE PIN 15.5-13.5 AWG .01 BR	TE Part #1-321898-0 DG 22-16 HT ALUMEL R 10
TE Part #326861 PIDG SPD 22-16 COMM 22-18MIL 6	TE Part #1740260-1 NECTOR S TUBE WHITE	TE Part #3-794618-8 08P MICRO MNL ASSY R/A HDR LF	TE Part #1740261-2 NECTOR S RING CLIP BLACK
TE Part #52041-1 TERMINAL,R PG 8 1/4	TE Part #1740451-2 NECTOR S OUTLET LV-2 YELLOW		

Documents

Product Drawings

NECTOR S PLUG HV-3 WHITE

English

CAD Files

3D PDF

3D



Customer View Model

[ENG\\_CVM\\_CVM\\_293388-2\\_C.2d\\_dxf.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_293388-2\\_C.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_293388-2\\_C.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

[NECTOR\\_S\\_LINE\\_CONNECTOR\\_BROCHURE](#)

English

Product Specifications

[Application Specification](#)

English

Agency Approvals

[UL Report](#)

English