



TECH FIELD - FLEX S3

Réf. : 70110



Suitable for :	Inside/Outside
Type :	Low shoe
Activity :	Construction / Manufacturing and assembly / Electronic Industry, ESD
Upper :	Water resistant full supple leather
Lining :	KENZO® + ON TEX® waterproof membrane, up to the toes, slipper feeling
Tongue :	Bellows tongue in ON STEAM® microfiber, lined with KENZO® + ON TEX® membrane, and padded
Ankle protection :	
Fastening :	Plastic hooks and round polyester black laces
Toe cap :	Ultralight and extra wide 200 joules, Composite LIGHT SYSTEM®
Midsole :	Composite FLEX SYSTEM®, anti-magnetic and thermal insulated
Insole :	Thermoformed in active carbon dual density foam, antistatic, ESD and antibacterial FRESH TECH®
Sole :	PU 2D, TECH SOLE® ankle anti-twist system, oil resistant FO, antistatic, HI-CI
Sole pattern :	Multi-purpose cleated indoor/outdoor outsole, well-defined heel, cleated arch, SRC standard
Weight (Kg/pair) :	1.000
Colors :	Black upper and dark grey/black outsole
Sizes :	35-48 (2-13)
Standard :	EN ISO 20345:2011 SRC WR / EN 61340-4-3 / DGUV 112-191
CE certificate of conformity N° :	0075/020/161/04/18/0585 EXT 07/04/18
Special features :	Waterproof membrane
Special features 2 :	Lateral reflective piece
Special features 3 :	WR (Water Resistant) certification

SPECIAL FEATURES

-  Integral 100% composite (Air System + Light System + Flex System)
-  Metal free, non magnetic
-  Water absorption and penetration resistance of upper (WRU)
-  Electro Static Discharge Standard EN 61340-5-1



GENERAL FEATURES

	Antistatic properties (A)	YES
	Heel energy absorption (E)	YES
	Abrasion resistance	YES
	Crampon sole	YES
	Heat-insulated sole (HI)	YES
	Cold-insulated sole (CI)	YES
	200 joule extra-wide toecap	YES
	Hyper-ventilated lining	YES
	Perforation-resistance 1100 N (P)	YES