


FEATURES

- **Annealed Copper Conductor:** Offers excellent conductivity and flexibility
- **Polyvinyl Chloride Jacket:** Provides durability and resistance to environmental factors
- **Screened Design:** Minimises electromagnetic interference for reliable signal transmission
- **Temperature Range -15 °C to 70 °C:** Suitable for various environmental conditions
- **Voltage Rating of 500 V:** Supports a wide range of control applications

**RS PRO 1.5 mm² Screened Control Cable,
100 m**

RS Stock No: 652-792



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This RS PRO screened control cable is designed for reliable signal transmission in industrial environments. With a 1.5 mm² cross-sectional area and a length of 100 m, it is ideal for applications requiring robust and consistent performance. The cable's screening provides excellent protection against electromagnetic interference, ensuring signal integrity.

General Specifications

Armoured	No
Conductor Material	Annealed Copper
Conductor Type	Plain
Jacket Colour	Grey
Product Type	Control Cable
Screened/Unscreened	Screened

Mechanical Specifications

Cable CSA	1.5 mm ²
Cable Length	100 m
Jacket Material	Polyvinyl Chloride
Number of Cores	3

Operation Environment Specifications

Maximum Operating Temperature	70 °C
Minimum Operating Temperature	-15 °C

Approvals

Standards/Approvals	ANSI-ESD S20.20:2021, BASEC, BS EN 50363-3, BS EN 60228, BS7671, IEC, RoHS
---------------------	--

Electrical Specifications

Voltage	500 V
---------	-------