

KU 01, KU 03, KU 04

KU 01 G.24 White
Nexans ref.: 10039056

Unscreened hook up wires, pairs and triples

Description

APPLICATIONS

Internal wiring in electronic equipment.

CONSTRUCTION

BASE CORE : KU 01

1. CONDUCTOR

stranded annealed tinned copper wires


2. INSULATION

ethylene and tetrafluorethylene copolymer (E.T.F.E).

KU 03 and KU 04

3. LAY UP

2 or 3 base cores.



Standards

National NF C 32-070/C1;
NF C 32-070/C2; NF C 93-524

Cable flexibility
Flexible

Operating temp. range
-55 ... 150 °C

RoHS conform
Yes

KU 01, KU 03, KU 04

KU 01 G.24 White
Nexans ref.: 10039056

Characteristics

Construction characteristics	
Conductor material	Tinned annealed copper
Insulation	ETFE
Electrical characteristics	
Maximum operating voltage	600 V
Mechanical characteristics	
Cable flexibility	Flexible
Usage characteristics	
Operating temperature, range	-55 .. 150 °C
RoHS conform	Yes



Cable flexibility
Flexible



Operating temp. range
-55 .. 150 °C



RoHS conform
Yes