

SL101 Digital Dispenser



An economical and versatile design that is suitable for most types of fluids and includes a suck-back feature to ensure that low viscosity liquids do not drip.

Micro controlled timer is programmable from 0.01 to 9999 seconds.

3 modes of operation are offered: 1) Manual will dispense as long as foot pedal is pressed; 2) Timed - will dispense according to an operator-set time; 3) Cycle - once the foot pedal is depressed, an operator programmed sequence including dispense time, wait or pause will run as programmed by the operator.



Features

- Digitally controlled program
- Easy to use touch sensitive controls
- Suitable for wide range of dispensing needs
- Barrel suck-back control ensures no drips
- Store up to 10 dispensing routines



Models

SL101-110	dispenser 110V
SL101-220	dispenser 220V CE

Models complete with accessory dispensing kit.
See page 36 for kit contents.

Specifications

Size:	8.63" x 8.50" x 2.63" (21.92 x 21.59 x 6.68cm)
Dispense time:	0.01 - 9999 seconds
Operation Modes:	Manual, Timed, Cycle
Internal Memory:	10 Memory Locations
Voltage:	110 VAC & 220 VAC
Air input:	70 to 100 psi (5 to 7 bar)
Air output:	1-100 psi (0.1 - 7 bar)
Standards:	CE approved, RoHS Compliant
Weight:	3.5 lbs (1.59 kg)



RoHS
COMPLIANT