Product datasheet Characteristics

ABE7R16T111

Sub-base with plug-in electromechanical relay ABE7 - 16 channels - relay 5 mm



Price*: 116.00 GBP



Main

Range of product	Advantys Telefast ABE7
Product or component type	Sub-base with plug-in electromechanical relay
Sub-base type	Output sub-base
[Us] rated supply voltage	1930 V conforming to IEC 61131-2
Number of channels	16
Connections - terminals	Screw type terminals, clamping capacity: 1 x 0.141 x 2.5 mm² AWG 26AWG 14 flexible without cable end
	Screw type terminals, clamping capacity: 1 x 0.141 x 1.5 mm² AWG 26AWG 16 flexible with cable end
	Screw type terminals, clamping capacity: 1 x 0.141 x 4 mm² AWG 26AWG 12 solid
	Screw type terminals, clamping capacity: 2 x 0.142 x 0.75 mm² AWG 26AWG 18 flexible with cable end
	Screw type terminals, clamping capacity: 2 x 0.142 x 1.5 mm² AWG 26AWG 16 solid

Complementary

Complementary		·
Supply circuit type	DC	
Product compatibility	ABR7S11	
Contacts type and composition	1 NO	
Status LED	1 LED for power ON 1 LED per channel for channel status	
Polarity distribution	Common distribution group of 4	
Short-circuit protection	1 A internal fuse, 5 x 20 mm, fast blow (PLC end)	
Mounting mode	By clips on 35 mm DIN rail By screws on surface mount with kit	
Supply current	<= 1 A	
Voltage drop on power supply fuse	0.3 V	
Current per output common	<= 5 A screw type terminals	
[Ui] rated insulation voltage	2000 V between terminals/mounting rails 300 V between coil circuit/contact circuits conforming to IEC 60947-1	

Current per module	<= 12 A	
[Uimp] rated impulse withstand voltage	2.5 kV	
Installation category	Il conforming to IEC 60664-1	
Tightening torque	0.6 N.m (with flat Ø 3.5 mm)	
Product weight	0.6 kg	

Environment

Product certifications	BV
	CSA
	DNV
	GL
	LROS (Lloyds register of shipping)
	UL
IP degree of protection	IP2x conforming to IEC 60529
Resistance to incandescent wire	750 °C, extinction time: <= 30 s conforming to IEC 60695-2-11
Shock resistance	15 gn for 11 ms conforming to IEC 60068-2-27
Vibration resistance	2 gn (f = 10150 Hz) conforming to IEC 60068-2-6
Resistance to electrostatic discharge	4 kV (contact) conforming to IEC 61000-4-2 level 3
	8 kV (air) conforming to IEC 61000-4-2 level 3
Resistance to radiated fields	10 V/m (260000001000000000 Hz) conforming to IEC 61000-4-3 level 3
Resistance to fast transients	2 kV conforming to IEC 61000-4-4 level 3
Ambient air temperature for operation	-560 °C conforming to IEC 61131-2
Ambient air temperature for storage	-4080 °C conforming to IEC 61131-2
Pollution degree	2 conforming to IEC 60664-1

Offer Sustainability


Green Premium product	
Compliant - since 0841 - Schneider Electric declaration of conformity	
Schneider Electric declaration of conformity	
Reference not containing SVHC above the threshold	
Reference not containing SVHC above the threshold	
Available	
End of life manual	
Available	
	Compliant - since 0841 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold Available End of life manual

Contractual warranty

Tonia diddi Harraniy	
Warranty period	18 months

ABE7R16T111


Dimensions



Product datasheet Mounting and Clearance

ABE7R16T111


Mounting



Product datasheet Connections and Schema

ABE7R16T111


HE10 16 Channels



Product datasheet Connections and Schema

ABE7R16T111

Wiring Diagram




- Inductive load
- (1) (2) (3) ABR7S11 (1F) - N/O Ith = 6 A (supplied for ABE7R16T111 and not supplied for ABE7P16T111)
 ABS7SC1B 24 V DC Imax. = 2 A (not supplied)

ABE7R16T111

Curves for Determining Cable Type and Length According to the Current

16-channel Sub-base




- L Cable length
- I_T Total current per sub base (A)
- I_A Average current per channel (mA)
- (1) TSXCDP••2 and ABFH20H••0 cables with c.s.a. 0.08 mm² (AWG 28).
- (2) TSXCDP••3 cables with c.s.a. 0.34 mm² (AWG 22).
- (3) Cables with c.s.a. 0.13 mm² (AWG 26).

The curves are given for a voltage drop of 1 V in the cable. For n volts tolerance, multiply the length determined from the graph by n.

ABE7R16T111

Electrical Durability (in Millions of Operating Cycles) Conforming to IEC 60947-5-1

DC Loads




DC12 control of resistive loads and of solid state loads isolated by optocoupler, I/R ≤ 1 ms.

(1) Resistive loads

(2) Inductive loads


DC13 curves



DC13 switching electromagnets, L/R ≤ 2 x (Ue x Ie) in ms, Ue: rated operational voltage, Ie: rated operational current (with a protective diode on the load, DC


AC Loads

AC12 curves



AC12 control of resistive loads and of solid state loads isolated by optocoupler, $\cos \phi \ge 0.9$.

AC15 curves



AC15 control of electromagnetic loads > 72 VA, make: $\cos \phi$ = 0.7, break: $\cos \phi$ = 0.4.