

# ST-6ES1N8A8003X - Cable connector



1242786

<https://www.phoenixcontact.com/in/products/1242786>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable connector, straight, Screw locking mechanism, M17, number of positions: 6+PE, contact connection type: Socket, shielded: yes, degree of protection: IP67, cable diameter range: 5 mm . .. 8 mm, number of positions: 7, connection method: Crimp connection, series: ST, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

## Your advantages

- Consistent EMC protection for reliable connection solutions in the industrial environment
- Crimping connection: vibration- and temperature-resistant assembly
- Flexible use: reliably connect various cable diameters
- Molded designs with preassembled cables on one or both sides

## Commercial data

Item number	1242786
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	*****
Product key	ABRBEA
GTIN	4063151399900
Weight per piece (including packing)	75 g
Weight per piece (excluding packing)	61.65 g
Customs tariff number	85366990
Country of origin	DE

# ST-6ES1N8A8003X - Cable connector



1242786

<https://www.phoenixcontact.com/in/products/1242786>

## Technical data

### Notes

Order information:	Order crimp contacts Ø 1 mm separately
Safety note	
Safety note	<p>WARNING: The connectors may not be plugged in or disconnected under load. Ignoring the warning or improper use may damage persons and/or property.</p> <ul style="list-style-type: none"><li>• WARNING: Commission properly functioning products only. The products must be regularly inspected for damage. Decommission defective products immediately. Replace damaged products. Repairs are not possible.</li><li>• WARNING: Only electrically qualified personnel may install and operate the product. They must observe the following safety notes. The qualified personnel must be familiar with the basics of electrical engineering. They must be able to recognize and prevent danger. The relevant symbol on the packaging indicates that only personnel familiar with electrical engineering are allowed to install and operate the product.</li><li>• The products are suitable for applications in plant, controller, and electrical device engineering.</li><li>• When operating the connectors in outdoor applications, they must be separately protected against environmental influences.</li><li>• Assembled products may not be manipulated or improperly opened.</li><li>• Only use mating connectors that are specified in the technical data of the standards listed (e.g. the ones listed in the product accessories online at <a href="https://www.phoenixcontact.com/products">phoenixcontact.com/products</a>).</li><li>• When using the product in direct connection with third-party manufacturers, the user is responsible.</li><li>• For operating voltages &gt; 50 V AC, conductive connector housings must be grounded</li><li>• Ensure that the protective or functional ground has been properly connected.</li><li>• VDE 0100/1.97 § 411.1.3.2 and DIN EN 60 204/11.98 § 14.1.3 are applicable when combining several circuits in a cable and/or connector</li><li>• Only use tools recommended by Phoenix Contact</li><li>• The installation notes/Design In documents online on the download page at <a href="https://www.phoenixcontact.com/products">phoenixcontact.com/products</a> must be observed for this product.</li><li>• Operate the connector only when it is fully plugged in and interlocked.</li><li>• Ensure that when laying the cable, the tensile load on the connectors does not exceed the upper limit specified in the standards.</li><li>• Observe the minimum bending radius of the cable. Lay the cable without twisting it.</li><li>• The connector warms up in normal operation. Depending on the ambient conditions, the surface of the connector can continue to warm up. In this case, the user is responsible for posting</li></ul>

# ST-6ES1N8A8003X - Cable connector



1242786

<https://www.phoenixcontact.com/in/products/1242786>

warnings (e.g. DIN EN ISO 13732-1:2008-12).

## Product properties

Product type	Circular connector (cable-side)
Series	ST
Application	Power
Number of positions	7
Connection profile	6+PE
Shielded	yes
Coding	N
Thread type	M17

## Material specifications

Seal material	FPM
Housing material	Metal

## Connection data

### Conductor connection

Connection method	Crimp connection
-------------------	------------------

## Electrical properties

### Contact

Contact diameter	1 mm
Max. current	14 A
Nominal voltage $U_N$	630 V
Overvoltage category	III
Degree of pollution	3
Rated surge voltage	6 kV

### Contact

Contact diameter	1 mm
------------------	------

## Connector

Type	straight
Direction of rotation	Standard

### Connection 1

Head design	Socket
-------------	--------

## Cable/line

External cable diameter	5 mm ... 8 mm
-------------------------	---------------

## Environmental and real-life conditions

### Ambient conditions

# ST-6ES1N8A8003X - Cable connector



1242786

<https://www.phoenixcontact.com/in/products/1242786>

Degree of protection	IP67
Ambient temperature (operation)	-40 °C ... 125 °C
Ambient temperature (storage/transport)	15 °C ... 25 °C
Altitude	3000 m
Permissible humidity (storage/transport)	50 % ... 65 %

# ST-6ES1N8A8003X - Cable connector


1242786

<https://www.phoenixcontact.com/in/products/1242786>




## Drawings

Schematic diagram



Connector pin assignment

Diagram



$I$  = current strength,  $\vartheta$  = ambient temperature, 3x 14 A + 2x 2 A constant


# ST-6ES1N8A8003X - Cable connector

1242786

<https://www.phoenixcontact.com/in/products/1242786>



Dimensional drawing



Technical drawings can be found under Downloads

# ST-6ES1N8A8003X - Cable connector



1242786

<https://www.phoenixcontact.com/in/products/1242786>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/in/products/1242786>



**cUL Recognized**

Approval ID: E335019-20111129



**UL Recognized**

Approval ID: E335019-20111129



**UL Recognized**

Approval ID: E153698-20140124



**cUL Recognized**

Approval ID: E153698-20140124

# ST-6ES1N8A8003X - Cable connector



1242786

<https://www.phoenixcontact.com/in/products/1242786>

## Classifications

### ECLASS

ECLASS-11.0	27440103
ECLASS-12.0	27440103
ECLASS-13.0	27440103

### ETIM

ETIM 9.0	EC003570
----------	----------



# ST-6ES1N8A8003X - Cable connector



1242786

<https://www.phoenixcontact.com/in/products/1242786>

## Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

# ST-6ES1N8A8003X - Cable connector



1242786

<https://www.phoenixcontact.com/in/products/1242786>

## Accessories

### ST-10KS0,06-1,00 - Crimp contact

1243216

<https://www.phoenixcontact.com/in/products/1243216>



Crimp contact, Socket, turned, contact diameter: 1 mm, crimp range: 0.06 mm<sup>2</sup> .. 1 mm<sup>2</sup>, Item is lead-free in accordance with RoHS II without Exemption 6c (Pb < 0.1 %)

---

### ST-Z0016 - Color coding

1617993

<https://www.phoenixcontact.com/in/products/1617993>

Color coding, color: green



# ST-6ES1N8A8003X - Cable connector

1242786

<https://www.phoenixcontact.com/in/products/1242786>




## ST-Z0017 - Color coding

1618049

<https://www.phoenixcontact.com/in/products/1618049>

Color coding, color: orange



---

## ST-Z0018 - Color coding

1618050

<https://www.phoenixcontact.com/in/products/1618050>

Color coding, color: black



# ST-6ES1N8A8003X - Cable connector

1242786

<https://www.phoenixcontact.com/in/products/1242786>



## PROT-M17PRO-IT-IP20 - Plastic protective cap

1055709

<https://www.phoenixcontact.com/in/products/1055709>

Plastic protective cap, M17, series: M17 PRO



---

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

[info@phoenixcontact.co.in](mailto:info@phoenixcontact.co.in)