

W92-X113-50

✓ ACTIVE

Potter & Brumfield | Potter & Brumfield W9


TE Internal #: 8-1393254-9

Circuit Breakers, Magnetic, Series Trip, Black Toggle Color, 277 VAC Voltage Rating AC, 50 A, 2, 10-32 Stud Termination, Potter & Brumfield W9

[View on TE.com >](#)



Relays, Contactors & Switches > Circuit Breakers



Circuit Breaker Type: **Magnetic**

Circuit Function: **Series Trip**

Illuminated: **No**

Toggle Color: **Black**

Voltage Rating AC: **277 VAC**

Features

Product Type Features

Illumination Type	No Light
Product Type	Circuit Breaker
Actuator Type	Toggle
Circuit Breaker Type	Magnetic
Illuminated	No
Toggle Color	Black

Configuration Features

	1.52 x 2.065 in
Earthing Switch	Without
Circuit Function	Series Trip

Electrical Characteristics

Voltage Rating AC	277 VAC
Circuit Breaker Current Rating	50 A
Interrupt Capacity	5000A @ 277VAC

Contact Features

Pole Configuration	2
Trip Time at 200%	.15 – 1.5 seconds

Termination Features



Circuit Breaker Termination Type	10-32 Stud
----------------------------------	------------

Mechanical Attachment

Series/Mounting Option	W9 (6-32 Mounting Threads)
Mounting Options	6-32 Mounting Threads
Circuit Breaker Mounting Type	Panel Mount

Dimensions

Circuit Breaker Size	63.5 mm[2.5 in]
----------------------	-----------------

Identification Marking

Stamped Marking Type	International I/O
----------------------	-------------------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2022 (224) Candidate List Declared Against: JUNE 2022 (224) SVHC > Threshold: Cadmium oxide (7.95% in Component Part) Article Safe Usage Statements: Use personal protective equipment as required. Do not eat, drink or smoke when using this product. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts



TE Part # 8-32589-2
TERMINAL,PIDG SPD 12-10 10



TE Part # 8-1393254-3
W92-X112-50=M6/M7/M9/W6/W7



TE Part # 2-36161-3
TERMINAL,PIDG R IR 12 10



TE Part # 6-1393254-5
W92-X1110-50=M6/M7/M9/W6/W7



TE Part # 9-1393254-4
W92-X152-50=M6/M7/M9/W6/W7

Also in the Series

Potter & Brumfield W9



Circuit Breakers(69)

Documents

- CAD Files
- 3D PDF
- 3D
- Customer View Model
- ENG_CVM_CVM_8-1393254-9_F.2d_dxf.zip
- English
- Customer View Model
- ENG_CVM_CVM_8-1393254-9_F.3d_igs.zip
- English
- Customer View Model
- ENG_CVM_CVM_8-1393254-9_F.3d_stp.zip
- English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages



W6/W9 Magnetic Hydraulic Circuit Breaker

English