

TVIP72500

IR HD 1080p Outdoor network dome camera

Tough outside, technological inside! Vandal-proof HD dome cameras with integrated IR LEDs produce finely-detailed, high-definition images in all environments. Whether used indoors or outdoors in daylight or at night, you will benefit from clear, fluid image results in HD and at a resolution of 720p. When the light intensity falls below a certain value, the colour camera switches to the light-sensitive B/W mode and the IR LEDs are activated. Both the data transmission and power supply can be fed through a network cable. One special feature is the analogue video output, which makes it easier to configure the camera using a test monitor.



Product highlights:

- Vandal-proof network outdoor dome camera with IP66
- HD resolution: 1080p
- Day/night function with integrated IR LEDs
- Analogue video output for service purposes
- PoE IEEE 802.3af
- Adjustable IR intensity

Your Partner:
ABUS-TEST
Linker Kreuthweg 5
86444 Affing
+49 (8207) 959900

TVIP72500

IR HD 1080p Outdoor network dome camera

Technical Data			
Sensor	1/4" Progressive Scan CMOS-Sensor	Power consumption	750 mA
Camera type	Network outdoor dome camera	Protection	IP66
Resolution	1920 x 1080, 1280 x 1024, 1280 x 960, 1280 x 720, 1024 x 768, 640 x 480, 320 x 240	Dimensions	(HxØ) 100 mm x 145 mm
Image elements	1920(H) x 1080(V)	Certificate	CE, RoHS, Reach
Lens	2.7–9 mm, F1.2		
Optical zoom	3.3x		
Digital zoom	10		
Day/night switching	IR cut can be swivelled electromagnetically		
Minimum illumination (color)	0.5 lux		
Minimum illumination (IR)	0		
Images per frames	MJPEG: 1920 x 1080 @ 25 fps, MJPEG: 640x480 @ 25 fps, MPEG-4: 1920 x 1080 @ 15 fps, MPEG-4: 640x480 @ 25 fps, H.264: 1920 x 1080 @ 25 fps, H.264: 640x480 @ 25		
Electronic-Shutter	1 ~ 1/7780 seconds		
White balance	yes		
Amplifier control	0–9		
Backlight compensation	BLC, WDR		
Motion detection	3 Zones		
Pre-/post-alarm storage	3 pre-alarm images, 1 event image, 3 post-alarm images		
Alarm input (NO/NC)	1		
Relais output	1		
Video output	1 x Cinch (FBAS)		
Alarming	E-Mail / FTP / HTTP notification / relay output / network drive		
SD card	Micro-SD-Karte		
IR LEDs	24		
IR range	15 m		
Network connection	RJ45 LAN		
Network protocols	Bonjour, TCP/IP, DHCP, PPPoE, ARP, ICMP, FTP, SMTP, DNS, NTP, UPnP, RTSP, RTP, HTTP, TCP, UDP, 3GPP/ISMA RTSP		
Encryption	HTTPS SSLv3		
Power supply	12 V DC		

Your Partner:
ABUS-TEST
 Linker Kreuthweg 5
 86444 Affing
 +49 (8207) 959900