

KombiSIGN 50 / Anschlusselement 845

Terminal element 12-230VAC/DC BK









ırt No.:	845.000.00	ϵ
Series:	KombiSIGN 50	7

MECHANICAL DATA			
Height	58 mm		
Diameter	52 mm		
Materials	PA-GF		
Housing colour	Black		
Protection category	IP54		
Connection	Screw terminals		
cross-sectional area maximum	1,50mm² / 16AWG		
Cable entry	Through hole		
Cable entry maximum	d = 9 mm		
Tension relief	Not present		
Type of fixing	Single-hole mounting Tube mounting		
Working temperature minimum	-20°C		
Working temperature maximum	+50°C		
Weight with packaging	92 g		
Product weight	78 g		

ELECTRICAL DATA				
Operating voltage	12-230V			
Operating voltage type	AC/DC			
Protection class	Protection class 2			
Pollution degree	3			
Overvoltage category	II			
Isolation voltage	Ui = 250V; Uimp = 2.500V			

APPROVAL DATA	
Conforms with CE	Yes
WEEE	Yes
Conforms with RED directive	No
Conform with ATEX-directive	No
Conforms with CCC	No
Conforms with UL	cULus
UL Type Rating	Type 12
Conforms with FCC	No
Conforms with IC	No
EAC certificate available	Yes
Conforms with AS-I	No
ICAO Certification	No
Conforms with GL	No


For additional installation and mounting information, refer to the appropriate user guide at www.werma.com. This printed copy is for information only and is subject to alteration.



KombiSIGN 50 / Anschlusselement 845

Terminal element 12-230VAC/DC BK

Conforms with RoHS CN	No
Conforms with VdS	No
MTTF-value [years]	45662



For additional installation and mounting information, refer to the appropriate user guide at www.werma.com. This printed copy is for information only and is subject to alteration.