

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name : RADIANT SENSE MB3000
Product code : 800333
Vaporizer : Aerosol
SKU # : R0260040

1.2. Relevant identified uses of the substance or mixture and uses advised against

1.2.1. Relevant identified uses

Main use category : Professional use
Use of the substance/mixture : Air care products
Odour agents

1.2.2. Uses advised against

No additional information available

1.3. Details of the supplier of the safety data sheet

Supplier

Newell Europe Sàrl
Chemin de Blandonnet 10
CH-1214 Vernier - Switzerland
T +44(0)870 5686824
SDS.RCP@newellco.com

Other

Newell Poland Services Sp. z o.o.
Plac Andersa 7
61-894 Poznań - Poland
T +44(0)870 5686824
www.rubbermaid.eu/contact

1.4. Emergency telephone number

Emergency number : +44(0)870 5686824

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No. 1272/2008 [CLP]

Aerosol, Category 1 H222;H229

Full text of H statements : see section 16

Adverse physicochemical, human health and environmental effects

No additional information available

2.2. Label elements

Labelling according to Regulation (EC) No. 1272/2008 [CLP]

Hazard pictograms (CLP) :



GHS02

Signal word (CLP) : Danger

Hazard statements (CLP) : H222 - Extremely flammable aerosol.
H229 - Pressurised container: May burst if heated.

Precautionary statements (CLP) : P210 - Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.
P211 - Do not spray on an open flame or other ignition source.
P251 - Do not pierce or burn, even after use.
P410+P412 - Protect from sunlight. Do not expose to temperatures exceeding 50 °C, 122 °F.

EUH-statements : EUH208 - Contains TETRAMETHYL ACETYLOCTAHYDRONAPHTHALENES, 2,4-DIMETHYL-3-CYCLOHEXENE CARBOXYALDEHYDE. May produce an allergic reaction.

2.3. Other hazards

This substance/mixture does not meet the PBT criteria of REACH regulation, annex XIII

This substance/mixture does not meet the vPvB criteria of REACH regulation, annex XIII

RADIANT SENSE MB3000

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable

3.2. Mixtures

Name	Product identifier	%	Classification according to Regulation (EC) No. 1272/2008 [CLP]
ISOPROPYL ALCOHOL	(CAS-No.) 67-63-0 (EC-No.) 200-661-7 (EC Index-No.) 603-117-00-0 (REACH-no) 01-2119457558-25	1 - 10	Flam. Liq. 2, H225 Eye Irrit. 2, H319 STOT SE 3, H336
TETRAMETHYL ACETYLOCTAHYDRONAPHTHALENES	(CAS-No.) 54464-57-2 (EC-No.) 259-174-3 915-730-3 (REACH-no) 01-2119489989-04	0.1 - 1	Aquatic Chronic 2, H411 Skin Irrit. 2, H315 Skin Sens. 1, H317
2,4-DIMETHYL-3-CYCLOHEXENE CARBOXALDEHYDE	(CAS-No.) 68039-49-6 (EC-No.) 268-264-1	0.1 - 1	Eye Irrit. 2, H319 Skin Irrit. 2, H315 Skin Sens. 1, H317 Aquatic Chronic 3, H412
DIPHENYL ETHER substance with a Community workplace exposure limit	(CAS-No.) 101-84-8 (EC-No.) 202-981-2	0.1 - 1	Aquatic Chronic 2, H411

Full text of H-statements: see section 16

SECTION 4: First aid measures

4.1. Description of first aid measures

- First-aid measures general : Never give anything by mouth to an unconscious person. If you feel unwell, seek medical advice (show the label where possible).
- First-aid measures after inhalation : Cough. Assure fresh air breathing. Allow the victim to rest.
- First-aid measures after skin contact : Remove affected clothing and wash all exposed skin area with mild soap and water, followed by warm water rinse.
- First-aid measures after eye contact : Direct contact with the eyes is likely to be irritating. Rinse immediately with plenty of water. Obtain medical attention if pain, blinking or redness persists.
- First-aid measures after ingestion : Rinse mouth. Do NOT induce vomiting. Obtain emergency medical attention.

4.2. Most important symptoms and effects, both acute and delayed

- Symptoms/effects after inhalation : Shortness of breath.

4.3. Indication of any immediate medical attention and special treatment needed

No additional information available

SECTION 5: Firefighting measures

5.1. Extinguishing media

- Suitable extinguishing media : Foam. Dry powder. Carbon dioxide. Water spray. Sand.
- Unsuitable extinguishing media : Do not use a heavy water stream.

5.2. Special hazards arising from the substance or mixture

- Fire hazard : Extremely flammable aerosol.
- Explosion hazard : Heat may build pressure, rupturing closed containers, spreading fire and increasing risk of burns and injuries.

5.3. Advice for firefighters

- Firefighting instructions : Use water spray or fog for cooling exposed containers. Exercise caution when fighting any chemical fire. Prevent fire fighting water from entering the environment. DO NOT fight fire when fire reaches explosives. Evacuate area.
- Protection during firefighting : Do not enter fire area without proper protective equipment, including respiratory protection.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

- General measures : No open flames. No smoking. Isolate from fire, if possible, without unnecessary risk. Remove ignition sources. Use special care to avoid static electric charges.

6.1.1. For non-emergency personnel

- Emergency procedures : Evacuate unnecessary personnel.

RADIANT SENSE MB3000

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

6.1.2. For emergency responders

Protective equipment : Equip cleanup crew with proper protection.
Emergency procedures : Ventilate area.

6.2. Environmental precautions

Prevent entry to sewers and public waters. Notify authorities if liquid enters sewers or public waters.

6.3. Methods and material for containment and cleaning up

Methods for cleaning up : Soak up spills with inert solids, such as clay or diatomaceous earth as soon as possible. Collect spillage. Store away from other materials.

6.4. Reference to other sections

See Heading 8. Exposure controls and personal protection.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Additional hazards when processed : Hazardous waste due to potential risk of explosion. Do not pierce or burn, even after use.
Precautions for safe handling : Wash hands and other exposed areas with mild soap and water before eating, drinking or smoking and when leaving work. Provide good ventilation in process area to prevent formation of vapour. Do not spray on an open flame or other ignition source.

7.2. Conditions for safe storage, including any incompatibilities

Technical measures : Comply with applicable regulations. Proper grounding procedures to avoid static electricity should be followed.
Storage conditions : Keep only in the original container in a cool, well ventilated place away from : Keep container closed when not in use. Do not expose to temperatures exceeding 50 °C/ 122 °F. Keep in fireproof place.
Incompatible products : Strong bases. Strong acids.
Incompatible materials : Sources of ignition. Direct sunlight. Heat sources.

7.3. Specific end use(s)

No additional information available

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

DIPHENYL ETHER (101-84-8)		
United Kingdom	Local name	Diphenyl ether
United Kingdom	WEL TWA (mg/m ³)	7 mg/m ³ vapour
United Kingdom	WEL STEL (mg/m ³)	14 mg/m ³ vapour
United Kingdom	Regulatory reference	EH40. HSE
ISOPROPYL ALCOHOL (67-63-0)		
United Kingdom	Local name	Propan-2-ol
United Kingdom	WEL TWA (mg/m ³)	999 mg/m ³
United Kingdom	WEL TWA (ppm)	400 ppm
United Kingdom	WEL STEL (mg/m ³)	1250 mg/m ³
United Kingdom	WEL STEL (ppm)	500 ppm
United Kingdom	Regulatory reference	EH40. HSE

8.2. Exposure controls

Personal protective equipment:

Avoid all unnecessary exposure.

Eye protection:

None under normal use. Chemical goggles or safety glasses

Respiratory protection:

None under normal use

Other information:

Do not eat, drink or smoke during use.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state : Liquid

RADIANT SENSE MB3000

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Appearance	: clear. Transparent.
Colour	: colourless to slightly yellow.
Odour	: characteristic.
Odour threshold	: No data available
pH	: No data available
Relative evaporation rate (butylacetate=1)	: No data available
Melting point	: Not applicable
Freezing point	: No data available
Boiling point	: Not applicable
Flash point	: No data available
Auto-ignition temperature	: None
Decomposition temperature	: No data available
Flammability (solid, gas)	: Extremely flammable aerosol.
Vapour pressure	: 3.5 - 4.5 bar
Relative vapour density at 20 °C	: No data available
Relative density	: 0.619 - 0.645
Solubility	: No data available
Log Pow	: No data available
Viscosity, kinematic	: No data available
Viscosity, dynamic	: No data available
Explosive properties	: No data available
Oxidising properties	: No data available
Explosive limits	: 1.8 - 19 vol %

9.2. Other information

No additional information available

SECTION 10: Stability and reactivity

10.1. Reactivity

No additional information available

10.2. Chemical stability

Extremely flammable aerosol. Contains gas under pressure; may explode if heated. Extreme risk of explosion by shock, friction, fire or other sources of ignition.

10.3. Possibility of hazardous reactions

Not established.

10.4. Conditions to avoid

Direct sunlight. Extremely high or low temperatures. Heat. Sparks. Open flame. Overheating.

10.5. Incompatible materials

Strong acids. Strong bases.

10.6. Hazardous decomposition products

fume. Carbon monoxide. Carbon dioxide.

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity (oral)	: Not classified
Acute toxicity (dermal)	: Not classified
Acute toxicity (inhalation)	: Not classified

2,4-DIMETHYL-3-CYCLOHEXENE CARBOXALDEHYDE (68039-49-6)

LD50 oral rat	4000 mg/kg
LD50 oral	2830 mg/kg
LD50 dermal	> 2000 mg/kg bodyweight

ISOPROPYL ALCOHOL (67-63-0)

LD50 oral rat	2000 mg/kg
LD50 oral	4396 mg/kg bodyweight
LD50 dermal rat	2000 mg/kg
LD50 dermal	12800 mg/kg bodyweight

RADIANT SENSE MB3000

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

ISOPROPYL ALCOHOL (67-63-0)	
LC50 inhalation rat (Dust/Mist - mg/l/4h)	46600 mg/l

Skin corrosion/irritation	: Not classified
Additional information	: Based on available data, the classification criteria are not met
Serious eye damage/irritation	: Not classified
Additional information	: Based on available data, the classification criteria are not met
Respiratory or skin sensitisation	: Not classified
Additional information	: Based on available data, the classification criteria are not met
Germ cell mutagenicity	: Not classified
Additional information	: Based on available data, the classification criteria are not met
Carcinogenicity	: Not classified
Additional information	: Based on available data, the classification criteria are not met
Reproductive toxicity	: Not classified
Additional information	: Based on available data, the classification criteria are not met

STOT-single exposure	: Not classified
Additional information	: Based on available data, the classification criteria are not met
STOT-repeated exposure	: Not classified
Additional information	: Based on available data, the classification criteria are not met
Aspiration hazard	: Not classified
Additional information	: Based on available data, the classification criteria are not met

RADIANT SENSE MB3000	
Vaporizer	Aerosol

Potential adverse human health effects and symptoms	: Based on available data, the classification criteria are not met.
---	---

SECTION 12: Ecological information

12.1. Toxicity

Acute aquatic toxicity	: Not classified
Chronic aquatic toxicity	: Not classified

ISOPROPYL ALCOHOL (67-63-0)	
LC50 fish 1	100 mg/l
EC50 Daphnia 1	100 mg/l
EC50 other aquatic organisms 1	13299 mg/l waterflea
EC50 other aquatic organisms 2	> 1000 mg/l

12.2. Persistence and degradability

RADIANT SENSE MB3000	
Persistence and degradability	Not established.

12.3. Bioaccumulative potential

RADIANT SENSE MB3000	
Bioaccumulative potential	Not established.

2,4-DIMETHYL-3-CYCLOHEXENE CARBOXALDEHYDE (68039-49-6)	
Log Pow	2.7

ISOPROPYL ALCOHOL (67-63-0)	
Log Pow	0.05

12.4. Mobility in soil

No additional information available

12.5. Results of PBT and vPvB assessment

RADIANT SENSE MB3000	
This substance/mixture does not meet the PBT criteria of REACH regulation, annex XIII	
This substance/mixture does not meet the vPvB criteria of REACH regulation, annex XIII	

12.6. Other adverse effects

Additional information	: Avoid release to the environment.
------------------------	-------------------------------------

RADIANT SENSE MB3000

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830






SECTION 13: Disposal considerations

13.1. Waste treatment methods

- Product/Packaging disposal recommendations : Dispose in a safe manner in accordance with local/national regulations. Container under pressure. Do not drill or burn even after use.
- Additional information : Flammable vapours may accumulate in the container.
- Ecology - waste materials : Avoid release to the environment.

SECTION 14: Transport information

In accordance with ADR / RID / IMDG / IATA / ADN

ADR	IMDG	IATA	ADN	RID
14.1. UN number				
1950	1950	1950	1950	1950
14.2. UN proper shipping name				
AEROSOLS	AEROSOLS	Aerosols, flammable	AEROSOLS	AEROSOLS
Transport document description				
UN 1950 AEROSOLS, 2.1, (D)	UN 1950 AEROSOLS, 2.1	UN 1950 Aerosols, flammable, 2.1	UN 1950 AEROSOLS, 2.1	UN 1950 AEROSOLS, 2.1
14.3. Transport hazard class(es)				
2.1	2.1	2.1	2.1	2.1
				
14.4. Packing group				
Not applicable	Not applicable	Not applicable	Not applicable	Not applicable
14.5. Environmental hazards				
Dangerous for the environment : No	Dangerous for the environment : No Marine pollutant : No	Dangerous for the environment : No	Dangerous for the environment : No	Dangerous for the environment : No
No supplementary information available				

14.6. Special precautions for user

- Overland transport

- Classification code (ADR) : 5F
- Special provisions (ADR) : 190, 327, 344, 625
- Limited quantities (ADR) : 11
- Excepted quantities (ADR) : E0
- Packing instructions (ADR) : P207, LP02
- Special packing provisions (ADR) : PP87, RR6, L2
- Mixed packing provisions (ADR) : MP9
- Transport category (ADR) : 2
- Special provisions for carriage - Packages (ADR) : V14
- Special provisions for carriage - Loading, unloading and handling (ADR) : CV9, CV12
- Special provisions for carriage - Operation (ADR) : S2
- Tunnel restriction code (ADR) : D

- Transport by sea

- Special provisions (IMDG) : 63, 190, 277, 327, 344, 959
- Limited quantities (IMDG) : SP277
- Excepted quantities (IMDG) : E0
- Packing instructions (IMDG) : P207, LP02
- Special packing provisions (IMDG) : PP87, L2
- EmS-No. (Fire) : F-D
- EmS-No. (Spillage) : S-U
- Stowage category (IMDG) : None

RADIANT SENSE MB3000

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

- Air transport

PCA Excepted quantities (IATA)	: E0
PCA Limited quantities (IATA)	: Y203
PCA limited quantity max net quantity (IATA)	: 30kgG
PCA packing instructions (IATA)	: 203
PCA max net quantity (IATA)	: 75kg
CAO packing instructions (IATA)	: 203
CAO max net quantity (IATA)	: 150kg
Special provisions (IATA)	: A145, A167
ERG code (IATA)	: 10L

- Inland waterway transport

Classification code (ADN)	: 5F
Special provisions (ADN)	: 19, 327, 344, 625
Limited quantities (ADN)	: 1 L
Excepted quantities (ADN)	: E0
Equipment required (ADN)	: PP, EX, A
Ventilation (ADN)	: VE01, VE04
Number of blue cones/lights (ADN)	: 1

- Rail transport

Classification code (RID)	: 5F
Special provisions (RID)	: 190, 327, 344, 625
Limited quantities (RID)	: 1L
Excepted quantities (RID)	: E0
Packing instructions (RID)	: P207, LP02
Special packing provisions (RID)	: PP87, RR6, L2
Mixed packing provisions (RID)	: MP9
Transport category (RID)	: 2
Special provisions for carriage – Packages (RID)	: W14
Special provisions for carriage - Loading, unloading and handling (RID)	: CW9, CW12
Colis express (express parcels) (RID)	: CE2
Hazard identification number (RID)	: 23

14.7. Transport in bulk according to Annex II of Marpol and the IBC Code

IBC code	: Not applicable.
----------	-------------------

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.1.1. EU-Regulations

Contains no REACH substances with Annex XVII restrictions
Contains no substance on the REACH candidate list
Contains no REACH Annex XIV substances

15.1.2. National regulations

No additional information available

15.2. Chemical safety assessment

No chemical safety assessment has been carried out

SECTION 16: Other information

Indication of changes:

Section	Changed item	Change	Comments
	Indication of changes	Added	
	Revision date	Added	
2.2	EUH-statements	Removed	
2.2	Precautionary statements (CLP)	Modified	

RADIANT SENSE MB3000

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

7.2	Technical measures	Modified	
7.2	Storage conditions	Modified	
8.2	Eye protection	Modified	
8.2	Hand protection	Removed	

Data sources : REGULATION (EC) No 1272/2008 OF THE EUROPEAN PARLIAMENT AND OF THE COUNCIL of 16 December 2008 on classification, labelling and packaging of substances and mixtures, amending and repealing Directives 67/548/EEC and 1999/45/EC, and amending Regulation (EC) No 1907/2006.

Other information : None.

Full text of H- and EUH-statements:

Aerosol 1	Aerosol, Category 1
Aquatic Chronic 2	Hazardous to the aquatic environment — Chronic Hazard, Category 2
Aquatic Chronic 3	Hazardous to the aquatic environment — Chronic Hazard, Category 3
Eye Irrit. 2	Serious eye damage/eye irritation, Category 2
Flam. Liq. 2	Flammable liquids, Category 2
Skin Irrit. 2	Skin corrosion/irritation, Category 2
Skin Sens. 1	Skin sensitisation, Category 1
STOT SE 3	Specific target organ toxicity — Single exposure, Category 3, Narcosis
H222	Extremely flammable aerosol.
H225	Highly flammable liquid and vapour.
H229	Pressurised container: May burst if heated.
H315	Causes skin irritation.
H317	May cause an allergic skin reaction.
H319	Causes serious eye irritation.
H336	May cause drowsiness or dizziness.
H411	Toxic to aquatic life with long lasting effects.
H412	Harmful to aquatic life with long lasting effects.
EUH208	Contains TETRAMETHYL ACETYLOCTAHYDRONAPHTHALENES, 2,4-DIMETHYL-3-CYCLOHEXENE CARBOXALDEHYDE. May produce an allergic reaction.

SDS EU ANNEX II NEWELL

This information is based on our current knowledge and is intended to describe the product for the purposes of health, safety and environmental requirements only. It should not therefore be construed as guaranteeing any specific property of the product