



Part Number : [2029881242](#)

Product Description : Mini-Fit TPA2/Sigma Female Crimp Terminal, Copper Alloy, Post-Plated Tin (Sn), 16 AWG, 1.98-2.55mm Insulation Diameter, Bag

Series Number : 202988

Status : Active

Product Category : Crimp Terminals

Packaging Alternative : [2029881241](#) (Reel)



Documents & Resources

Drawings

[2029881242 sd.pdf](#)

[2029880003-000.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[AS-172718-0000-001.pdf](#)

[2131370000-AS-000.pdf](#)

[2029880001-PS-000.pdf](#)


[2029880002-PS-000.pdf](#)

[1727180003-TS-000.pdf](#)

[2029880001-TS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006 
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)

EU RoHS	Compliant per EU 2015/863
---------	---------------------------

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	202988
Description	Mini-Fit TPA2/Sigma Female Crimp Terminal, Copper Alloy, Post-Plated Tin (Sn), 16 AWG, 1.98-2.55mm Insulation Diameter, Bag
Application	Power, Wire-to-Wire, Wire-to-Board
Comments	See product specification for current derating information.
Product Name	Mini-Fit Sigma,Mini-Fit TPA2
UPC	191128369596

Electrical

Current - Maximum per Contact	13.5A
Voltage - Maximum	600V AC/DC

Physical

Durability (mating cycles max)	30
--------------------------------	----

Gender	Female
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.211/g
Packaging Type	Bag
Plating min - Mating	2.500µm
Plating min - Termination	2.500µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.98-2.55mm
Wire Size (AWG)	16
Wire Size mm ²	N/A

Mates With / Use With

Use with Part(s)

Description	Part Number
Mini-Fit TPA2 and Mini-Fit Sigma Dual Row Receptacle Housings	<u>172708</u>

Application Tooling

Global

Description	Part Number
Hand Crimp Tool for Mini-Fit TPA2 Male and Female Crimp Terminals, 16 AWG, Large and Small Insulation Grips	<u>2002181700</u>