

Product data sheet

Specifications

GT bend, Mureva Tube GT, diameter 32mm, IP40, grey



IMT53332

Main

range of product	Mureva
Product or component type	Bend
Function available	GT-function
Mounting location	Indoor Outdoor
Nominal cross section	607 mm²
Diameter	External: 32 mm Internal: 27.8 mm
Colour tint	Grey (RAL 7035)

Complementary

Quantity per set	1 piece
Ambient air temperature for operation	-5...60 °C
Material	PVC (polyvinyl chloride)
Standards	IEC 61386

Environment

IP degree of protection	IP40
IK degree of protection	IK07
Environmental characteristic	Non-flame propagating
Product certifications	NF

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	3.500 cm
Package 1 Width	3.500 cm
Package 1 Length	33.000 cm
Package 1 Weight	90.000 g
Unit Type of Package 2	CAR
Number of Units in Package 2	40
Package 2 Height	40.000 cm
Package 2 Width	30.000 cm

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Package 2 Length	40.000 cm
Package 2 Weight	4.016 kg
Unit Type of Package 3	PAM
Number of Units in Package 3	1080
Package 3 Height	135.000 cm
Package 3 Width	100.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	123.432 kg

Contractual warranty

Warranty (in months)	18
----------------------	----



Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)



Environmental footprint

Total lifecycle Carbon footprint	2 kg CO2 eq.
Carbon footprint of the manufacturing phase [A1 to A3]	2 kg CO2 eq.
Carbon footprint of the distribution phase [A4]	0.1 kg CO2 eq.
Carbon footprint of the installation phase [A5]	0 kg CO2 eq.
Carbon footprint of the use phase [B2, B3, B4, B6]	0 kg CO2 eq.
Carbon footprint of the end-of-life phase [C1 to C4]	0.7 kg CO2 eq.
Environmental Disclosure	Product Environmental Profile

Use Better



Materials and Substances

Packaging made with recycled cardboard	No
Packaging without single use plastic	No
SCIP Number	90215406-b6bf-44f8-b463-8540d32a6f6b
EU RoHS Directive	Compliant
REACH Regulation	Reference contains Substances of Very High Concern above the threshold

Use Longer



Lifetime extension

Repair	No
--------	----

Use Again



Repack and remanufacture

Recyclability potential, in %	0
End of life manual availability	No need of specific recycling operations
Take-back	No