


Part Number : [2239380100](#)

Product Description : 1.00mm Pitch, Rely-On PCB Header, Single Row, Vertical, Surface Mount, 0.38µm Gold (Au) Plating, Inner Positive Lock, 10 Circuits, Black

Series Number : 223938

Status : Active

Product Category : PCB Headers and Receptacles



Documents and Resources

Drawings

[2239380100_sd.pdf](#)

[2239389200-SPK-200.pdf](#)

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Specifications

[2239360000-PS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	223938
Description	1.00mm Pitch, Rely-On PCB Header, Single Row, Vertical, Surface Mount, 0.38µm Gold (Au) Plating, Inner Positive Lock, 10 Circuits, Black
Application	Wire-to-Board
Component Type	PCB Header
Product Name	Rely-On
UPC	198282614333

Electrical

Current - Maximum per Contact	2.5A
Voltage - Maximum	100V AC (RMS)/DC

Physical

Breakaway	No
Circuits (Loaded)	10
Circuits (maximum)	10
Color - Resin	Black
Durability (mating cycles max)	30
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	No

Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Resin	Polyamide (PA)
Net Weight	352.050/mg
Number of Rows	1
Orientation	Vertical
Packaging Type	Embossed Tape on Reel
PCB Locator	No
PCB Retention	Yes
Pitch - Mating Interface	1.00mm
Plating min - Mating	0.380µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Shrouded
Stackable	No
Temperature Range - Operating	-55° to +125°C
Termination Interface Style	Surface Mount

Mates With / Use With

Mates with Part(s)

Description	Part Number
Rely-On 1.0 Single Row Crimp Housings	<u>223936</u>