

CGA4J3X7S2A474M125AE

TDK Item Description : CGA4J3X7S2A474MT***S



Equivalent C2012X7S2A474M for Automotive

Application & Main Feature

Automotive Grade (Soft Termination)

Series

CGA4(2012) [EIA CC0805]

Dimensions

L 2.00mm +0.45,-0.2mm
W 1.25mm +0.25,-0.2mm
T 1.25mm +0.25,-0.2mm
B 0.20mm Min.
G 0.50mm Min.

Temperature Characteristic

X7S (-55 to 125 degC +/-22%)

Rated Voltage

2A (100Vdc)

Capacitance

470nF

Capacitance Tolerance

M (+/-20%)

Dissipation Factor


5% Max.

Insulation Resistance


1.06Gohm Min.

AEC-Q200


Yes




DC Bias Characteristic




|Z|, ESR vs. Freq. Characteristics




Temperature Characteristics



Cap. vs. Freq. Characteristic



Ripple Temperature Rise Characteristics



All specifications are subject to change without notice.

January 4, 2016