

Commercial status: Commercialised



Main

Range	Acti9
Product name	Acti9 iDD40 XA
Product or component type	Residual current breaker with overcurrent protection (RCBO)
Device short name	IDD40T XA
Device application	Distribution
Poles description	1P + N
Number of protected poles	1
Neutral position	Left
[In] rated current	16 A
Network type	AC
Trip unit technology	Thermal-magnetic
Curve code	C
Earth-leakage sensitivity	30 mA
Earth-leakage protection time delay	Instantaneous
Earth-leakage protection class	Type AC
Breaking capacity	4500 A Icn at 230 V AC 50 Hz conforming to EN/IEC 61009-2-1 6 kA Icu at 230 V AC 50 Hz conforming to EN/IEC 60947-2
Suitability for isolation	Yes conforming to EN/IEC 60947-2
Quality labels	NF

Complementary

Device location in system	Outgoer
Network frequency	50 Hz
[Ue] rated operational voltage	230 V AC 50 Hz
Magnetic tripping limit	5...10 x In
Residual current tripping technology	Voltage independent
[Ics] rated service breaking capacity	4500 A 100 % x Icn at 230 V AC 50 Hz conforming to EN/IEC 61009-2-1
Rated breaking and making capacity	I _{dm} 3000 A at 230 V AC 50 Hz conforming to EN/IEC 61009-2-1
Limitation class	3 conforming to EN/IEC 61009-2-1
[Ui] rated insulation voltage	400 V AC 50 Hz
[Uimp] rated impulse withstand voltage	4 kV
Surge current	250 A
Contact position indicator	Yes
Control type	Toggle
Local signalling	ON/OFF indication Fault indication
Mounting mode	Clip-on
Mounting support	DIN rail
Comb busbar and distribution block compatibility	Top or bottom: tooth
9 mm pitches	4
Height	91 mm

Width	36 mm
Depth	73 mm
Net weight	200 g
Colour	White
Mechanical durability	20000 cycles
Electrical durability	20000 cycles
Locking options description	Sealable Padlocking device
Connections - terminals	Screwless type terminals top comb busbar Tunnel type terminals bottom 1...10 mm ² flexible Tunnel type terminals bottom 1...16 mm ² rigid
Wire stripping length	14 mm for bottom connection
Tightening torque	2 N.m bottom
Earth-leakage protection	Integrated

Environment

Standards	EN/IEC 60947-2 EN/IEC 61009-2-1
Product certifications	CE
IP degree of protection	IP20 conforming to IEC 60529 IP40 (modular enclosure) conforming to IEC 60529
Pollution degree	3
Overvoltage category	III conforming to IEC 60364
Electromagnetic compatibility	8/20 µs impulse withstand, 250 A conforming to EN/IEC 61009-2-1
Relative humidity	95 % at 55 °C
Operating altitude	2000 m
Ambient air temperature for operation	-5...60 °C
Ambient air temperature for storage	-40...85 °C

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Compliant EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins

Contractual warranty

Warranty	18 mois
----------	---------