

Endress+Hauser Pressure sensor PMP21-AA1A1NBWBj

Compact gauge or absolute pressure transducer with metal sensor.



Picture for reference only. Product appearance may vary based on configuration

The Cerabar PMP21 is a very compact pressure transmitter with piezo-resistive sensor that can measure absolute or gauge pressure from 400mbar up to 40bar (depending on configuration) in gases, vapors, liquids and dust with an accuracy of 0.3%. The PMP21 is designed to withstand the harsh conditions in the process industry with ingress protection grades up to IP 68 and high quality materials like 316L.

- Easy usability
- High performance
- Long term stability
- High material quality

Configuration of PMP21-AA1A1NBWBj:

Approval:	AA	Non-hazardous area
Output:	1	4-20mA
Electrical Connection:	A	Cable 5m, IP66/68 NEMA Type 4X/6P Encl.
Sensor Range:	1N	6bar/600kPa/90psi gauge, overload: 24bar/2.4MPa/360psi
Calibration; Unit:	B	Sensor range; mbar/bar
Process Connection:	WBj	Thread ISO228 G1/2 EN837, 316L

Alternative part number: PMP21-2CV2/0