

Main

Range	New Unica
Product or component type	Push-button + indicator
Device presentation	Mechanism with fixing frame
[Ue] rated operational voltage	230 V AC at 50...60 Hz
Number of modules	2 modules
Fixing mode	Screws or claws
Colour tint	Anthracite
Main colour tint	Anthracite





Complementary

Light block colour	White
Bulb type	LED
Connections - terminals	Screw terminals
Clamping connection capacity	<= 2 x 2.5 mm ² for flexible cable(s) <= 2 x 2.5 mm ² for rigid cable(s)
Material	PC: mechanism cover PC (polycarbonate) GF10 FR: casing Thermoplastic ABS-UV stabilised: rocker switch CuZn37: terminals PBT (polybutylene terephthalate) GF30: release button PC (polycarbonate) GF10 FR: fixing frame
Standards	EN 62094-1 CE
Directives	2014/35/EU - low voltage directive
Ambient air temperature for operation	5...45 °C
Ambient air temperature for storage	-5...50 °C
Embedding depth	21 mm
Depth	31 mm
Width	74.5 mm
Height	74.5 mm
Net weight	0.068 kg
Resistance to chemical agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

Environment

IK degree of protection	IK03
IP degree of protection	IP2XC

Offer Sustainability

REACH Regulation	 REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant  EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
Sustainable packaging	Yes
RoHS exemption information	 Yes
China RoHS Regulation	 China RoHS Declaration