



**Part Number :** [14442106](#)  
**Product Description :** 2.54mm Pitch SL Insulation  
Displacement Connector Assembly, Male, Single Row,  
Version D, Back Ribs, for Wire Size 28 AWG, 0.38µm  
Gold (Au), 6 Circuits  
**Series Number :** 70475  
**Status :** Active  
**Product Category :** Connector Housings  
**Engineering Number :** 70475-0950



## Documents & Resources

### Drawings


[014442106\\_sd.pdf](#)  
[PK-70873-0001-001.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)  
[SOLIDWORKS](#)  
[Creo](#)

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC

- Low-Halogen

#### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### Substances of Interest

- PFAS

#### EU RoHS Certificate of Compliance

#### Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	Connector Housings
Series	70475
Description	2.54mm Pitch SL Insulation Displacement Connector Assembly, Male, Single Row, Version D, Back Ribs, for Wire Size 28 AWG, 0.38µm Gold (Au), 6 Circuits
Comments	Terminals Preloaded
Component Type	Housing
Product Name	SL
UPC	800755033076

### Agency

CSA	LR19980
UL	E29179

### Electrical

Voltage - Maximum	250V
-------------------	------

### Physical

Circuits (Loaded)	6
Circuits (maximum)	6

Color - Resin	Black
Durability (mating cycles max)	50
Entry Angle	Vertical
Flammability	94V-0
Gender	Male
Glow-Wire Capable	No
Lock to Mating Part	None
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	Polyester Alloy
Net Weight	0.746/g
Number of Rows	1
Packaging Type	Tube
PCB Retention	None
Pitch - Mating Interface	2.54mm
Polarized to Mating Part	No
Stackable	Yes
Temperature Range - Operating	-40° to +105°C
Termination Interface Style	IDT or Pierce
Wire/Cable Type	Discrete Wire, Ribbon Cable
Wire Insulation Diameter	1.35mm max.
Wire Size (AWG)	28

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
2.54mm SL Interim Clips	<u><a href="#">70013</a></u>

---

## Application Tooling

### Global

Description	Part Number
Ribbon Cable Tool Kit, Press Not Included	<u>622016600</u>